



Pass and Seymour  
TradeMaster® LED/CFL/Incandescent Single Pole/3-Way Toggle Slide Dimmer, Preset, Black  
Part No. TSDCL303PBK



TradeMaster® Toggle Slide Dimmer is designed for use with compact fluorescent or LED lighting fixtures. This single pole 3-way switch can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability. This switch offers dependability and a lifetime warranty.

## Features & Benefits

Matches appearance of standard Pass and Seymour toggle switch  
Interchangeable face covers are available in seven different colors  
Lifetime warranty

All models are Single Pole/3-Way capable  
Highest wattage rating

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Gloss	UPC Number	785007215946
Country Of Origin	China	Features	Color Change Kit, Low-End Trim (Dim Range)
Switch Type	Single Pole 3-Way, Slider, Toggle	Number of Switches	1
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

### Dimensions

Product Width US	2.5 in	Product Depth US	1.4 in
Product Height US	4.19 in		

### Technical Information

Preset	Yes	Load Rating	120V 2.5A 300W (LED), 120V 4.5A 450W (CFL), 120V 700W (Halogen), 120V 700W (Incandescent)
--------	-----	-------------	---

Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	CFL, Halogen, Incandescent, LED
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Trim/Adjustment Level	Wheel	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC