



Pass and Seymour
TradeMaster® LED/CFL/Incandescent Single Pole/3-Way Toggle Slide Dimmer, Preset, Tri-Color
Part No. TSDCL303PTC



TradeMaster® Toggle Slide Dimmer is designed for use with compact fluorescent or LED lighting fixtures. This single pole 3-way switch can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability. This switch offers dependability and a lifetime warranty.

Features & Benefits

Matches appearance of standard Pass and Seymour toggle switch	All models are Single Pole/3-Way capable
Interchangeable face covers are available in seven different colors	Highest wattage rating
Lifetime warranty	

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Finish	Gloss	UPC Number	785007215977
Country Of Origin	China	Features	Color Change Kit, Low-End Trim (Dim Range)
Switch Type	Single Pole 3-Way, Slider, Toggle	Number of Switches	1
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	1.4 in
Product Height US	4.19 in		

Technical Information

Preset	Yes	Load Rating	120V 2.5A 300W (LED), 120V 4.5A 450W (CFL), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz

Number of Gangs	1	Bulb Compatibility	CFL, Halogen, Incandescent, LED
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Trim/Adjustment Level	Wheel	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC