



Pass and Seymour  
TradeMaster® Toggle Slide Dimmer Low Voltage Single Pole/3-Way, 700VA, Light Almond  
Part No. TSDLV703PLA



700 VA, Preset, Single Pole/3-Way Toggle Slide Dimmer

## Features & Benefits

- Matches appearance of standard Pass & Seymour toggle switch
- Interchangeable face covers are available in seven different colors
- Lifetime warranty
- All models are Single Pole/3-Way capable
- Highest wattage rating

## Specifications

### General Info

|                    |                                   |                    |  |
|--------------------|-----------------------------------|--------------------|--|
| Product Line       | Pass & Seymour                    | Color              | Light Almond                               |
| Finish             | Gloss                             | UPC Number         | 785007216103                               |
| Country Of Origin  | China                             | Features           | Color Change Kit, Low-End Trim (Dim Range) |
| Switch Type        | Single Pole 3-Way, Slider, Toggle | Number of Switches | 1  |
| Application Sector | Residential                       | Warranty Type      | Limited Lifetime Warranty                  |

### Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 2.5 in  | Product Depth US | 1.4 in |
| Product Height US | 4.19 in |                  |        |

### Technical Information

|        |     |             |   |
|--------|-----|-------------|---|
| Preset | Yes | Load Rating | 120V 700VA (MLV - Halogen), 120V 700VA (MLV - Incandescent) |
|--------|-----|-------------|---|

|                       |                   |                       |                       |
|-----------------------|-------------------|-----------------------|-----------------------|
| Dimming Compatibility | Forward Phase     | Frequency Rating      | 60 Hz                 |
| Number of Gangs       | 1                 | Bulb Compatibility    | Halogen, Incandescent |
| Number of Poles       | Single Pole 3-Way | Trim/Adjustment Level | Wheel                 |
| Requires Neutral Wire | No                | Indoor/Outdoor        | Indoor                |
| Mounting Type         | Wall Box          | Wire Connection Type  | Screw Terminals       |
| Voltage               | 120 VAC           |                       |                       |