



Pass and Seymour  
TradeMaster® Toggle Slide Dimmer Low Voltage Single Pole/3-Way, 700VA, White  
Part No. TSDLV703PW



700 VA, Preset, Single Pole/3-Way Toggle Slide Dimmer

## Features & Benefits

- Matches appearance of standard Pass & Seymour toggle switch
- Interchangeable face covers are available in seven different colors
- Lifetime warranty
- All models are Single Pole/3-Way capable
- Highest wattage rating

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007216097
Country Of Origin	China	Features	Color Change Kit, Low-End Trim (Dim Range)
Switch Type	Single Pole 3-Way, Slider, Toggle	Number of Switches	1
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

### Dimensions

Product Width US	2.5 in	Product Depth US	1.4 in
Product Height US	4.19 in		

### Technical Information

Preset	Yes	Load Rating	120V 700VA (MLV - Halogen), 120V 700VA (MLV - Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	Halogen, Incandescent
Number of Poles	Single Pole 3-Way	Trim/Adjustment Level	Wheel
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC		