



Replace your standard switch with the new Toggle Slide Dimmer by Legrand. The new Toggle Slide Dimmer offering has been optimized for today's complicated dimmable bulb market. Different bulbs require different dimming solutions and Legrand has you covered for all your lighting needs. The ergonomic slider was designed with the end user in mind, making it easier to adjust in the dark or on the run.

Compatible with CFL/LED and Incandescent/Halogen dimmable bulbs (with the exception of 0-10V LED drivers), these dimmers feature constant memory that returns lights to the previous level after a power failure for automatic control and convenience.

## Features & Benefits

No neutral wire required

Calibration button allows users to adjust minimum and maximum trim levels for a wide range of CFL and LED bulbs

New aesthetically pleasing ergonomic design allows for easier operation

Constant memory returns lights to previous levels after a power failure

Convenient operation – combines ON/OFF toggle switch with separate slider for dimming control

Screw-pressure-plate backwire terminals save time, space and money

Preset, Single Pole and 3-Way operation.

Lifetime warranty

## Specifications

### General Info

|                    |                         |                    |                           |
|--------------------|-------------------------|--------------------|---------------------------|
| Product Line       | Pass & Seymour          | Color              | White                     |
| Finish             | Matte                   | Country Of Origin  | China                     |
| Switch Type        | Rocker, Slider          | Number of Switches | 1                         |
| Application Sector | Commercial, Residential | Warranty Type      | Limited Lifetime Warranty |
| Type               | Dimmer                  |                    |                           |

### Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.73 in | Product Depth US | 1.4 in |
| Product Height US | 4.19 in |                  |        |

### Technical Information

|                 |                    |                    |                                 |
|-----------------|--------------------|--------------------|---------------------------------|
| Amperage        | 2.1 A              | Bulb Compatibility | CFL, Halogen, Incandescent, LED |
| Number of Poles | 3-Way, Single Pole | Wattage            | 300 W                           |
| Voltage         | 120.0 V            |                    |                                 |