



Pass and Seymour
Two-Gang Commercial Metal Recessed TV Box, White
Part No. TV2MW



All steel construction. Accepts MC, AC, Rommex or Conduit. Devices not included (image to the right is shown with devices installed).

Features & Benefits

All Steel Construction

Side mount or face mount

Adjustable for 1/2" to 1 1/2" sheet rock

Accepts MC, AC, Romex or Conduit

Integral 35 cubic inch electrical box

Mounts to either side of steel studs

Concentric knock outs 1/2" to 3/4"

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007030174	Country Of Origin	China
Material	Cold Rolled Steel	Features	Recessed
Number of Knockouts	2	Application Sector	Commercial, Residential
Standard	cULus, RoHS	Warranty Type	1-Year Limited Warranty
Type	Recessed TV Boxes		

Dimensions

Product Width US	7.6 in	Product Weight US	2.85 lb
Product Depth US	3.5 in	Product Height US	6.9 in

Product Length US	6.9 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	2	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Cable Entry	Back	Box Shape	Square
-------------	------	-----------	--------

Mounting Type	Screw Mount
---------------	-------------
