



Wiremold
Plug-In Outlet Center Unit / 120V/15A/24 long/8 O/L /lighted switch/6' cord
Part No. UL300BC



Eight outlets, lighted switch, rugged gray aluminum housing, 15A, 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 24" (609mm). Receptacle center-to-center 2" (51mm). Snap-on, slide-off mounting.

Features & Benefits

Eight outlets, lighted switch, rugged gray aluminum housing, 15A, 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 24" (609mm). Receptacle center-to-center 2" (51mm). Snap-on, slide-off mounting.

Specifications

General Info

Product Line	Wiremold	Color	Aluminum, Gray
UPC Number	786776043006	Country Of Origin	Mexico
Product Series	Plug-In Outlet Center	Receptacle Type	Simplex
Number of Receptacles	8	Features	Lighted Switch, Resettable Circuit Breaker
Application Sector	Commercial, Residential	Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

Dimensions

Product Width US	2.0 in	Product Weight US	2.5 lb
Product Length US	24.0 in	Receptacle Spacing	2 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Phase	Single	Cord Length	6 ft
-------	--------	-------------	------

Amperage	15 A	Enclosure Type	Aluminum
----------	------	----------------	----------

Wiring Method	Cord-ended	NEMA Configuration Code	5-15P, 5-15R
---------------	------------	-------------------------	--------------

Mounting Type	Slide-off, Snap-on	Voltage	125.0 V
---------------	--------------------	---------	---------

Environmental Conditions	Dry interior locations
--------------------------	------------------------