



**Wiremold**  
**Plug-In Outlet Center Unit / 120V/20A/8 O/L /lighted switch/6' cord**  
Part No. ULB820-6



Eight 20A, 120V, 60Hz, 2500 watt outlets, lighted switch, putty white aluminum housing, 6' (1.8m) 12/3 SJT black cord with NEMA5-20 plug. Length 17 1/4" (438mm). Receptacle center-to-center 1 1/2" (38mm). Snap-on slide-off mounting.

## Features & Benefits

Eight 20A, 120V, 60Hz, 2500 watt outlets, lighted switch, putty white aluminum housing, 15' (4.6m) 12/3 SJT black cord with NEMA5-20 plug. Length 17 1/4" (438mm). Receptacle center-to-center 1 1/2" (38mm). Snap-on slide-off mounting.

## Specifications

### General Info

Product Line	Wiremold	Color	White
UPC Number	786776043372	Country Of Origin	Mexico
Material	Aluminum	Product Series	Plug-In Outlet Center
Receptacle Type	Simplex	Number of Receptacles	8
Features	Lighted Switch, Resettable Circuit Breaker	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

### Dimensions

Product Width US	2.0 in	Product Weight US	3.4 lb
------------------	--------	-------------------	--------

---

Product Length US	17.063 in	Receptacle Spacing	1.5 in
-------------------	-----------	--------------------	--------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Phase	Single	Cord Length	6 ft
-------	--------	-------------	------

---

Amperage	20 A	Enclosure Type	Aluminum
----------	------	----------------	----------

---

Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
----------------	--------	---------------	------------

---

NEMA Configuration Code	5-20P, 5-20R	Mounting Type	Snap-on, Slide-off
-------------------------	--------------	---------------	--------------------

---

Location Rating	Dry	Voltage	120.0 V
-----------------	-----	---------	---------

---

Environmental Conditions	Dry interior locations		
--------------------------	------------------------	--	--

---