



20A configuration. Four outlets, white finish. 15' (4.6m) cord. Length 10 3/4" (237mm). Receptacle center-to-center 1 1/2" (38mm). cTUVus Listed as Medical Electrical Equipment. Suitable for use where Article 517 of the NEC requires Hospital Grade Outlets.

Features & Benefits

20A configuration. Four outlets, white finish. 6' (1.8m) cord. Length 10 3/4" (237mm). Receptacle center-to-center 1 1/2" (38mm). cTUVus Listed as Medical Electrical Equipment. Suitable for use where Article 517 of the NEC requires Hospital Grade Outlets.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776180749
Country Of Origin	Mexico	Receptacle Type	Double
Number of Receptacles	6	Standard	cTUVus Listed
Type	PIOC		

Dimensions

Product Width US	2.0 in	Product Length US	14.17 in
------------------	--------	-------------------	----------

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Frequency Rating	50/60 Hz	Amperage	20 A
Mounting Type	Snap-on, Slide-off	Voltage	120.0 V
Environmental Conditions	Dry interior locations		