



Wiremold  
**GFCI PLUGMOLD 6FT IVORY 11 OUTLETS AND SELF TEST GFCI MOD**  
Part No. V20GB606TRGFI6



Plugmold® Multioutlet Systems are available in a wide variety of lengths and fittings and in a variety of finishes to provide versatile solutions for many applications. Plugmold options include single or alternating circuits, standard or isolated ground receptacles, GFCI protection, tamper-resistant protection, USB charging, Snapicoil® harnesses of prewired receptacles, and cord-ended units. Plugmold® Multioutlet Systems are available in black or ivory ScuffCoat™ finish, painted white or gray enamel steel, stylish stainless steel, anodized aluminum and durable textured ivory nonmetallic. The painted steel product works with many types of decor and is paintable to integrate with most color schemes. Durable stainless steel and anodized aluminum Plugmold products are corrosion-resistant, making them ideal for labs.

## Features & Benefits

Compact, low profile appearance. Enhanced aesthetics and ideal for installations within minimal spaces.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776188110
Country Of Origin	United States	Number of Receptacles	11
Application Sector	Commercial	Standard	cULus Listed Multioutlet assemblies: File E15191 Guide PVGT. Meets Article 380 of NEC.
Type	Plugmold		

### Dimensions

Product Width US	1.3 in	Product Weight US	3.78 lb
Product Depth US	0.75 in	Product Length US	1.3 in

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Trade Programs

---

USMCA	Yes
-------	-----

---

Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

Technical Information

---

Amperage	20 A	Enclosure Type	Steel
Voltage	125.0 V	Environmental Conditions	Dry interior locations

---