



Twistouts permit use of three parallel raceway runs on each side. Base has 1/2" and 1" concentric trade size KOs and a 1 13/16" (46mm) x 2 7/8" (73mm) rectangular KO to mount on a one-gang in-wall outlet box. Cover accepts devices with mounting screw centers of 2 3/4", 3 1/2", or 4 1/16" (70mm, 89mm, or 104mm), and canopy fixtures no larger than 4 5/8" (117mm) in diameter. With 5736 Blank Cover, this fitting can be used as junction box, pull box, etc. NOTE: Certified to Canadian Safety Standards for sale in Canada. When ordering these products, change the "V" color prefix to "VC" to denote the Canadian versions.

Features & Benefits

Twistouts permit use of three parallel raceway runs on each side. Base has 1/2" and 1" concentric trade size KOs and a 1 13/16" (46mm) x 2 7/8" (73mm) rectangular KO to mount on a one-gang in-wall outlet box.

Cover accepts devices with mounting screw centers of 2 3/4", 3 1/2", or 4 1/16" (70mm, 89mm, or 104mm), and canopy fixtures no larger than 4 5/8" (117mm) in diameter.

With 5736 Blank Cover, this fitting can be used as junction box, pull box, etc. NOTE: Certified to Canadian Safety Standards for sale in Canada. When ordering these products, change the "V" color prefix to "VC" to denote the Canadian versions.

Specifications

General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776070385	Country Of Origin	United States
Application Sector	Commercial, Residential	Standard	cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E4751 Guide RJPR. Meets Article 386 of NEC. Meets Section 12-1600 of CEC.
Type	Raceway		

Dimensions

Product Width US	4.75 in	Product Weight US	0.79 lb
------------------	---------	-------------------	---------

Product Depth US	1.375 in	Product Length US	4.75 in
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Voltage	600.0 V		