



The Vantage ELDS4-1-DIN, Dimming Station is a 4 channel dimmer that connects to the Vantage Control System. It is powered from a local line feed, and communicates with the system through the Vantage 2-wire Station Bus.

Features & Benefits

Controls 4 electronic loads of up to 480 watts @ 240v	Controls 2 electronic loads of up to 960 watts @ 240v, (Two consecutive load outputs must not be used under these conditions)
Load actuator buttons with status indicators on front face	Exclusively for electronic loads
Connects to system via 2 wire Vantage Station Bus	Diagnostics / Station Status LED

Specifications

General Info

Product Line	Vantage	UPC Number	804428036586
Country Of Origin	China	Application Sector	Commercial, Residential
Warranty Type	5-Year	Type	Dimmer

Dimensions

Product Width US	6.18 in	Product Weight US	1.4 lb
Product Depth US	2.76 in	Product Height US	3.4 in

Listing Agencies / 3rd Party Agencies

CE Certified	Yes
--------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Compatibility	InFusion	Storage Humidity	5-95% RH (Non-Condensing)
Current Rating	4 A	Indoor/Outdoor	Indoor
Operating Temperature	0°-40°C, 32°-104°F	Mounting	DIN Rail
Voltage	120 to 277 V		
