



Vantage
InFusion Secondary Power Enclosure - 2 Module
Part No. ISPE-2-IC

The InFusion Secondary Power Enclosure (ISPE) economically extends the load capacity of the Vantage System, extending system capacity from the Main Power Enclosure (IMPE)

Features & Benefits

Extends the Main Controller's load capacity	Features plug-and-play fittings for all modules
Comes factory installed with a low-voltage wiring harness eliminating the need to wire between modules	Installs between standard 16-inch/40.64-centimeter on center framing or may be surface mounted
Custom fitted hinged door for recessed or surface installs	Allows visual diagnostics of enclosure components through ventilation slots in the cover
Enclosure Terminal Boards interchangeable from new modules to legacy modules	

Specifications

General Info

Product Line	Vantage	UPC Number	804428053927
Country Of Origin	United States	Application Sector	Commercial, Residential
Warranty Type	5-Year	Type	Enclosure

Dimensions

Product Width US	14.5 in	Product Weight US	29.0 lb
Product Depth US	4.0 in	Product Height US	35.0 in

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	cUL Listed	Yes
--------------	-----	------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Compatibility	InFusion	Wire Gauge	16-18 AWG
Storage Humidity	5-95% RH (Non-Condensing)	Frequency Range	50-60 Hz
Indoor/Outdoor	Indoor	Operating Temperature	0°-40°C, 32°-104°F
Voltage	120 to 277 V		
