



The Radiolink Enabler is a wireless transceiver that adds RF communication to the Vantage Main Controller. Since a communication wire is not needed, it is a true retrofit solution allowing Vantage automation in existing structures.

Features & Benefits

- Allows up to 60 RF stations per Enabler
- Reliable 900 MHz wireless with adaptive multi-channel hopping to avoid interference
- 100 foot transmission radius per enabler (over 4 million cubic feet)
- Easily connects to the existing rS-232 and power connections on the main terminal board
- Plug-and-play design

Specifications

General Info

Product Line	Vantage	Color	Black
UPC Number	840624100454	Country Of Origin	China
Application Sector	Commercial, Residential	Warranty Type	5-Year
Type	Wireless Enabler		

Dimensions

Product Width US	2.4 in	Product Depth US	0.9 in
Product Height US	7.8 in		

Listing Agencies / 3rd Party Agencies

FCC Compliant	Yes
---------------	-----

Additional Information

Energy Savings No

Technical Information

Max Distance Support	100 ft	Compatibility	InFusion, Qlink
Signal Type	RF	Storage Humidity	5-95% RH (Non-Condensing)
Power Supply	12VDC	Indicator	Receive LED, Transmit LED
Antenna	Yes	Input Voltage	12 V
Number of Channels	25	Operating Temperature	32°-158°F
Mounting	External to Enclosure	Type of Indicators	LED
