



# Wattstopper Wattstopper PLUS Emergency Lighting Load Control Enclosed Relay with Auxiliary Contacts, Yellow Part No. ESRLB-U

The ESRLB-U Emergency Relay allows for local power sense, bringing fixtures to full brightness on loss of normal power. The ESRLB-U is UL924 certified and includes a 6A Single Pole Single Throw relay as well as a built in 0-10V break.



## Features & Benefits

- 6 Amp SPST Relay
- Includes 0-10V emergency override
- Plenum rated
- Slim form factor suitable for in fixture mounting
- No EM side power draw

## Specifications

### General Info

Product Line	Wattstopper	Color	Yellow
Finish	Matte	Material	Plastic
Features	Emergency Relay	Installation Location	Above Ceiling
Application Sector	Commercial	Standard	cUL, RoHS, UL, CE
Warranty Type	5-Year	Type	Emergency Load Controller

### Dimensions

Product Width US	5.63 in	Product Weight US	6.8 oz
Product Depth US	1.4 in	Product Height US	1.0 in

### Listing Agencies / 3rd Party Agencies

CE Certified	Yes	cUL Listed	Yes
--------------	-----	------------	-----

### Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
Energy Savings	Yes		
<b>Technical Information</b>			
Operating Temperature Min	-30 °F	Compatibility	Wattstopper PLUS Wired, Wattstopper PLUS Wireless
Has Battery	No	Contact Rating	120VAC, 6A, 277VAC, 5A
Operating Temperature Max	140 °F	Throw Type	Single Throw
Number of Poles	Single Pole	Number of Relays	1
Indicator	Relay Status LED	Input Voltage	120 to 277 VAC
Line Frequency	50 Hz, 60 Hz	Indoor/Outdoor	Indoor
Mounting Type	Fixture Embedded	Current Draw	6 mA
Operating Temperature	-30°-140°F	Operating Humidity	5-95% RH (Non-Condensing)
Location Rating	Dry	Wire Connection Type	Wire Leads