




Wiremold
20GB306TRUSB 3' Plugmold® Multioutlet System with USB
Part No. WH20GB306TRUSB



3' Plugmold Multioutlet USB system

Features & Benefits

USB charging. 2.4A USB type A receptacle charges faster than other USB receptacles and is compatible with USB 2.0 and 3.0 type devices.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

This product meets the material restrictions of RoHS.

Tamper-resistant receptacles. Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code® Tamper-Resistant requirements.

Compact design. Eliminates the need for bulky AC adapters.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776182651
Country Of Origin	United States	Number of Receptacles	5
Application Sector	Commercial	Standard	cULus Listed Multioutlet assemblies: File E15191 Guide PVGT. Meets Article 380 of NEC.
Type	Plugmold		

Dimensions

Product Width US	1.3 in	Product Depth US	0.75 in
------------------	--------	------------------	---------

Product Length US	1.3 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

Technical Information

Frequency Rating	60 Hz	Amperage	20 A
------------------	-------	----------	------

Enclosure Type	Steel	Voltage	125.0 V
----------------	-------	---------	---------

Environmental Conditions	Dry interior locations
--------------------------	------------------------
