



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

Features & Benefits

- Meets new Tamper Resistant requirements for 2008 NEC Section 406.11. Provides additional protection from burns and other injuries. Mandated for residential applications.
 - Built-in shutter system. Prevents the insertion of unwanted objects such as hairpins, keys and nails. Providing additional protection for occupants including small children.
 - Available in 3' & 5' [914mm & 1.5m] lengths with 6" [305mm] receptacle spacing. Provides additional power access in smaller, more confined areas. Multiple lengths present more mounting options.
 - 15A Proprietary Simplex Decorator Receptacle. Functional and aesthetically pleasing, matches any décor.
 - Steel or aluminum construction. Superior strength for residential applications. Providing years of protection and convenience.
 - Designed for surface mounting. Easier and more convenient installation. Eliminates the need to break through walls.
 - Multiple finishes. Available in ivory, gray, white, black, stainless steel and anodized aluminum to accommodate a wide range of applications.
 - Multiple power feed options. Provide clean, attractive installations with concealed power sources.
 - Custom options available. Custom configurations and finish options are also available. Consult the factory for more information.
 - cULus Listed.
- This product meets the material restrictions of RoHS.

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776180107	Country Of Origin	United States
Number of Receptacles	12	Application Sector	Residential/Commercial
Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7	Type	Plugmold

Dimensions

Product Width US	72.0 in	Product Weight US	3.49 lb
Product Volume US	74.52 cu in	Product Depth US	0.75 in

Product Height US 1.38 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber E15191 cULus Listed Yes

Buy American Act Compliance

NAFTA Yes

Additional Information

RoHS Conformant Yes Product Environmental Profile Yes

Technical Information

Frequency Rating 60 Hz Amperage 15 A

Enclosure Type Steel Voltage 125.0 V

Environmental Conditions Dry interior locations
