



Wiremold
24 in Ceiling Panel
Part No. LCP-PS-2-2424



Standardized, utility ceiling panel designed to deliver overhead power, data, gas and air through a single, spec-ready solution. The 12" x 24" painted white steel panel fits standard ceiling grids and supports flexible service configurations for evolving lab environments and more.

Features & Benefits

Standardized & Fully Specifiable. Simplifies and streamlines design, bidding and approvals.

Faster Alternative to Custom Fabrication. A faster, simpler path than traditional shop-built solutions.

Ideal for healthcare, research facilities, commercial, education and quick service restaurant environments.

Integrated & Field-Configurable Services. Power, data and lab utilities like air, gas and vacuum in one panel.

Clean, Consistent Aesthetic. Delivers a uniform ceiling appearance with repeatable quality.

Designed for Change. Reconfigurable/updatable for changing needs.

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776200775	Country Of Origin	United States
Material	Steel	Conduit Size	3/4 in
Number of Receptacles	10	Construction	Sheet Metal
Installation Location	Drop Ceiling	Number of Knockouts	4
Application Sector	Commercial, Education, Healthcare, Healthcare, Hospitality, Industrial	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Electrical Ceiling Panel		

Dimensions

Product Width US	24.0 in	Product Depth US	3.53 in
Product Length US	24.0 in	Knockout Size	1/2 in, 3/4 in

Trade Programs

USMCA	Yes	BAA	Yes
-------	-----	-----	-----

Additional Information

RoHS Compliant	Yes	Energy Savings	No
----------------	-----	----------------	----

Technical Information

Seismic Tested	No	Is Tamper-Resistant	No
Is Pre-Wired	No	Number of Gangs	10
Amperage	60 A	Number of Compartments	2
Load Capacity	150 lb	Indoor/Outdoor	Indoor
Cable Entry	1/2 in, 3/4 in, Knockout	Mounting Type	Threaded Rod
Voltage	600.0 V		
