



Wiremold
100A Power Pedestal 1G 16In Black
Part No. XPPPSHA16-BK



The 100A Pin & Sleeve Outdoor Power Pedestal delivers reliable, high-amperage power in a permanent, UL-listed solution designed for demanding outdoor environments. Built to support applications where traditional 30A or 60A options fall short, this pedestal enables outdoor spaces to accommodate larger loads without relying on temporary power or custom solutions. Engineered for long-term outdoor use, the pedestal combines high-power capability with durable, weather-rated construction and a clean, architectural form. Flexible configuration options—including multiple heights and finish choices—allow it to integrate seamlessly into campuses, public spaces and event environments while supporting higher-amperage power needs with reliable, long-lasting performance.

Features & Benefits

High Amperage: 100 Amps is highest amperage on the market

Variety of Finishes: Available in green, brown, silver and black to meet any outdoor aesthetic

Pre-Wired & Unwired Options: Choose prewired for quick installation or unwired for full on-site customization

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776200867	Country Of Origin	United States
Material	Steel	Application Sector	Commercial, Entertainment, Hospitality, Parks, Transit
Type	Power Pedestal		

Dimensions

Product Width US	7.638 in	Product Depth US	7.638 in
Product Height US	16.378 in	Product Length US	5.984 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E479489	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Is Pre-Wired	No	Service Capacity	Single
--------------	----	------------------	--------

Number of Gangs	1	Amperage	100 A
-----------------	---	----------	-------

Enclosure Type	NEMA 3R	Maximum Amperage Supported	100 A
----------------	---------	----------------------------	-------
