



Pass and Seymour
Weatherproof Cover for Flanged Inlet-Outlet
Part No. WPG1



Industrial Grade Weatherproof Lift Cover For Flanged Inlet/Outlet,
1.96-inch Diameter Opening to Accommodate 15/20A Straight Blade,
15A Turnlok®, 20403 Power Interrupter

Features & Benefits

- Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
- Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.
- WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.
- Covers fit all competitive inlets and outlets.
- Tamper-proof hinge features permanent, locked-in pins for added security.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Weatherproof	Application Sector	Industrial
Standard	UL listed		

Dimensions

Product Width US	2.85 in	Product Height US	4.57 in
------------------	---------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	15 A	Number of Outlets	1
----------	------	-------------------	---

