



Pass and Seymour  
Thermoplastic Weatherproof Covers for Flanged Inlet-Outlet  
Part No. WPG2



Industrial Grade Weatherproof Lift Cover, 2.32-inch Diameter Opening to Accommodate 20A/30A Turnlok®, For Flanged Inlet/Outlet

## Features & Benefits

- Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.
- Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.
- Covers fit all competitive inlets and outlets.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
- WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.
- Tamper-proof hinge features permanent, locked-in pins for added security.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	Mexico
Standard	UL Listed, CSA		

### Dimensions

Product Width US	2.85 in	Product Height US	4.57 in
------------------	---------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Amperage	20 A	Number of Outlets	1
----------	------	-------------------	---