



Pass and Seymour
4-in Round Outdoor Cluster Cover, White
Part No. WPRB13W

Weatherproof 4-inch Round Outdoor Cluster Cover, Blank 3 Hole
1/2-in With Gasket and Screws, Bronze



Features & Benefits

Wide range of rectangular and round covers.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

Kits available combining fixtures, lamp covers, and accessories.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007117325
Country Of Origin	India	Features	Weatherproof
Wall Plate Type	Custom	Application Sector	Industrial
Standard	UL listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof Cover		

Dimensions

Product Width US	4.625 in	Product Depth US	1.0 in
Product Height US	4.625 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Technical Information

Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
----------------	--------	---------------	-------------

Number of Outlets	3
-------------------	---