



Pass and Seymour

Wide Slide 0-10V Preset Dimmer with Integrated Power Pack, Tri-Color
Part No. WS4FBL3PTC



For use on 0-10V, 4-wire, 120V & 277V fluorescent dimming ballasts and LED fixtures.

Features & Benefits

- For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts.
- Low voltage pig tails labeled separately.
- Green LED glows when OFF to make dimmer easy to find in the dark.
- Wider slide control for easier dimming operation.
- For covering patents, see www.legrand.us/patents.
- Convenient operation combines ON/OFF Decorator switch with separate slider for dimming control.
- Preset, Single Pole and 3-Way Operation.
- Sleek, ergonomic P&S Decorator style matches other Decorator devices.
- Built-in power pack included.

Specifications

General Info

| | | | |
|--------------------|----------------------------|--------------|----------------|
| Color | White, Light Almond, Ivory | UPC Number | 785007047721 |
| Country Of Origin | China | Product Line | Pass & Seymour |
| Application Sector | Residential/Commercial | Standard | cULus, RoHS |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|--------------------------|--|-----------------|-------------|
| Wattage | 450 W | Number of Poles | Single Pole |
| Voltage | 120 V | Connection | Wire Leads |
| Frequency Rating | 120VAC 60Hz Hz | Load | CFL/LED |
| Environmental Conditions | Humidity: Less than 95% non condensing | | |