



Pass and Seymour
Wide Slide Series 0-10V Fluorescent/LED Single Pole/3-Way Slide Dimmer, Preset, Tri-Color
Part No. WS4FBL3PTC



For use on 0-10V, 4-wire, 120V & 277V fluorescent dimming ballasts and LED fixtures.

Features & Benefits

For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts

Convenient operation combines ON/OFF Decorator switch with separate slider for dimming control

Low voltage pig tails labeled separately

Preset, Single Pole and 3-Way Operation

Green LED glows when OFF to make dimmer easy to find in the dark

Sleek, ergonomic Pass and Seymour Decorator style matches other Decorator devices

Wider slide control for easier dimming operation

Built-in power pack included

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Finish	Matte	UPC Number	785007047721
Country Of Origin	China	Features	Color Change Kit, Low-End Trim (Dim Range)
Switch Type	Rocker, Single Pole 3-Way, Slider	Number of Switches	1
Application Sector	Commercial, Hospitality, Residential	Standard	cULus, RoHS
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

Product Height US4.25 in

Listing Agencies / 3rd Party Agencies

cULus ListedYes

Technical Information

Preset	Yes	Load Rating	120V 10A (Fluorescent), 120V 10A (LED), 277V 5A (Fluorescent), 277V 5A (LED)
Dimming Compatibility	0-10 V	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	Fluorescent, LED
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120/277 VAC	Environmental Conditions	Humidity: Less than 95% non condensing