



Pass and Seymour
Wide Slide Series 0-10V Fluorescent/LED Single Pole/3-Way Slide Dimmer, Preset, White
Part No. WS4FBL3PW



For use on 0-10V, 4-wire, 120V & 277V fluorescent dimming ballasts and LED fixtures.

Features & Benefits

For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts	Convenient operation combines ON/OFF Decorator switch with separate slider for dimming control
Low voltage pig tails labeled separately	Preset, Single Pole and 3-Way Operation
Green LED glows when OFF to make dimmer easy to find in the dark	Sleek, ergonomic Pass and Seymour Decorator style matches other Decorator devices
Wider slide control for easier dimming operation	Built-in power pack included

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Switch Type	Push, Slider
Number of Switches	1	Application Sector	Residential/Commercial
Standard	cULus, RoHS	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Wire Leads
Amperage	10 A	Bulb Compatibility	Fluorescent, LED
Number of Poles	3-Way, Single Pole	Voltage	120.0 V
Load	CFL, LED	Environmental Conditions	Humidity: Less than 95% non condensing

