



For use on 0-10V, 4-wire, 120V & 277V fluorescent dimming ballasts and LED fixtures.

Features & Benefits

- For use with 0-10V, 4 wire, 120V 10A/277V 5A LED and fluorescent dimming drivers/ballasts
- Low voltage pig tails labeled separately
- Green LED glows when OFF to make dimmer easy to find in the dark
- Wider slide control for easier dimming operation
- Convenient operation combines ON/OFF Decorator switch with separate slider for dimming control
- Preset, Single Pole and 3-Way Operation
- Sleek, ergonomic Pass and Seymour Decorator style matches other Decorator devices
- Built-in power pack included

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Switch Type	Push, Slider
Number of Switches	1	Application Sector	Residential/Commercial
Standard	cULus, RoHS	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Wire Leads
Amperage	10 A	Bulb Compatibility	Fluorescent, LED
Number of Poles	3-Way, Single Pole	Voltage	120.0 V
Load	CFL, LED	Environmental Conditions	Humidity: Less than 95% non condensing

