



Pass and Seymour
Wide Slide Series CFL/LED/Incandescent Single Pole/3-Way Slide Dimmer, Non-Preset, White
Part No. WSCL450W



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

Convenient Operation - Combines ON/OFF Decorator-style switch with separate slider for dimming control

Constant memory returns lights to previous level after a power failure

Sleek, ergonomic design that matches well with other decorator products

Higher ratings

Single-pole operation

Screw-pressure-plate back wire terminals save time, space and money

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Switch Type	Slider
Number of Switches	1	Application Sector	Residential/Commercial
Standard	cULus, RoHS	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Bulb Compatibility	CFL, Incandescent, LED	Number of Poles	3-Way, Single Pole
Wattage	450 W	Voltage	120.0 V
Load	CFL, LED	Environmental Conditions	Humidity: Less than 95% non condensing
