



Pass and Seymour
Wide Slide Series CFL/LED/Incandescent Single Pole/3-Way Slide Dimmer, Non-Preset, White
Part No. WSCL450W



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

| | |
|--|--|
| Convenient Operation - Combines ON/OFF Decorator-style switch with separate slider for dimming control | Constant memory returns lights to previous level after a power failure |
| Sleek, ergonomic design that matches well with other decorator products | Higher ratings |
| Single-pole operation | Screw-pressure-plate back wire terminals save time, space and money |
| Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz | |

Specifications

General Info

| | | | |
|--------------------|---------------------------|--------------------|--|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007040425 |
| Country Of Origin | China | Features | Color Change Kit, Non-Low-End Trim (Dim Range) |
| Switch Type | Single Pole, Slider | Number of Switches | 1 |
| Application Sector | Residential | Standard | cULus, RoHS |
| Warranty Type | Limited Lifetime Warranty | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.75 in | Product Depth US | 1.25 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 4.25 in |
|-------------------|---------|

Technical Information

| | | | |
|-----------------------|---------------------------------|-----------------------------|---|
| Preset | No | Load Rating | 120V 450W (CFL), 120V 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent) |
| Dimming Compatibility | Forward Phase | Frequency Rating | 60 Hz |
| Number of Gangs | 1 | Minimum Load Recommendation | 10 W |
| Bulb Compatibility | CFL, Halogen, Incandescent, LED | Number of Poles | Single Pole |
| Wire Size | #14 - #10 AWG | Trim/Adjustment Level | Wheel |
| Requires Neutral Wire | No | Indoor/Outdoor | Indoor |
| Mounting Type | Wall Box | Wire Connection Type | Screw Terminals |
| Voltage | 120 VAC | Environmental Conditions | Humidity: Less than 95% non condensing |