



**Wiremold**  
**Desktop Power Center Slim, 2 Outlets, USB A/C, White, 6ft Cord**  
Part No. WSPC220CWH



Desktop Power Center with two (2) or three (3) 15A tamper resistant power receptacles and two (2) smart USB ports, one (1) USB-A and one (1) USB-C, that provide 3.1A. Includes a screw-in mounting plate for forward-facing outlets, under-table mount bracket, and clamp mounting kit. Available with either a 6' (1.83m) or 10' (3.05m) power cord.

## Features & Benefits

- Multiple options:** Two versions with reliable power and charging – one with three (3) tamper-resistant power outlets and two (2) USB charging ports (3.1A) and one with two (2) tamper-resistant power outlets and two (2) USB charging ports (3.1A).
- Intelligent and energy efficient:** Smart charging capability that recognizes devices and when to shut off during peak loads.
- Easy connection to power sources:** 6' (1.83m) or 10' (3.05m) 14 gauge cord easily reaches walls and floors.
- Simple and flexible installation:** Mounting kits include options for both horizontal and vertical applications.
- Less clutter, more functionality:** A sleek slim design fits unobtrusively on work surfaces.
- Seamlessly blends into your space:** Two color choices that work with any environment.
- Table Thickness:** Supports tables from 0.5" to 1.5" for the clamp mount. Under table bracket mount supports 1" to 1.5".
- Included Mounting Kit:** Includes several mounting options for use under and above table surfaces for any environment.

## Specifications

### General Info

|                       |              |                    |                      |
|-----------------------|--------------|--------------------|----------------------|
| Product Line          | Wiremold     | Color              | White                |
| UPC Number            | 786776192568 | Country Of Origin  | China                |
| Number of Receptacles | 2            | Application Sector | Commercial           |
| Warranty Type         | 1-Year       | Type               | Desktop Power Center |

### Dimensions

---

|                  |         |                   |         |
|------------------|---------|-------------------|---------|
| Product Width US | 2.25 in | Product Height US | 2.25 in |
|------------------|---------|-------------------|---------|

---

|                   |        |
|-------------------|--------|
| Product Length US | 4.9 in |
|-------------------|--------|

---

### Listing Agencies / 3rd Party Agencies

---

|            |     |                   |                  |
|------------|-----|-------------------|------------------|
| ETL Listed | Yes | ETL ListingNumber | 103010043BOX-001 |
|------------|-----|-------------------|------------------|

---

### Additional Information

---

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

---

### Technical Information

---

|                     |     |             |      |
|---------------------|-----|-------------|------|
| Is Tamper-Resistant | Yes | Cord Length | 6 ft |
|---------------------|-----|-------------|------|

---

|                |   |                |        |
|----------------|---|----------------|--------|
| Number of USBs | 2 | Indoor/Outdoor | Indoor |
|----------------|---|----------------|--------|

---

|               |            |                   |   |
|---------------|------------|-------------------|---|
| Mounting Type | On Surface | Number of Outlets | 2 |
|---------------|------------|-------------------|---|

---