



Desktop Power Center with two (2) or three (3) 15A tamper resistant power receptacles and two (2) smart USB ports, one (1) USB-A and one (1) USB-C, that provide 3.1A. Includes a screw-in mounting plate for forward-facing outlets, under-table mount bracket, and clamp mounting kit. Available with either a 6' (1.83m) or 10' (3.05m) power cord.

## Features & Benefits

- Multiple options: Two versions with reliable power and charging – one with three (3) tamper-resistant power outlets and two (2) USB charging ports (3.1A) and one with two (2) tamper-resistant power outlets and two (2) USB charging ports (3.1A).
  - Intelligent and energy efficient: Smart charging capability that recognizes devices and when to shut off during peak loads.
- Easy connection to power sources: 6' (1.83m) or 10' (3.05m) 14 gauge cord easily reaches walls and floors.
  - Simple and flexible installation: Mounting kits include options for both horizontal and vertical applications.
- Less clutter, more functionality: A sleek slim design fits unobtrusively on work surfaces.
  - Seamlessly blends into your space: Two color choices that work with any environment.
- Table Thickness: Supports tables from 0.5" to 1.5" for the clamp mount. Under table bracket mount supports 1" to 1.5".
  - Included Mounting Kit: Includes several mounting options for use under and above table surfaces for any environment.

## Specifications

### General Info

Product Line	Wiremold	Color	White
UPC Number	786776198621	Country Of Origin	China
Number of Receptacles	3	Application Sector	Commercial
Warranty Type	1-Year		

### Dimensions

Product Width US	2.25 in	Product Height US	2.25 in
Product Length US	6.0 in		

### Listing Agencies / 3rd Party Agencies

---

ETL Listed	Yes	ETL ListingNumber	103010043BOX-001
------------	-----	-------------------	------------------

---

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Is Tamper-Resistant	Yes	Cord Length	10 ft
---------------------	-----	-------------	-------

---

Number of USBs	2	Indoor/Outdoor	Indoor
----------------	---	----------------	--------

---

Mounting Type	On Surface	Number of Outlets	3
---------------	------------	-------------------	---

---