



The single service 2-gang Outdoor Ground Box is made from a UV rated nonmetallic material and has been designed to withstand the harsh outdoor environments. The box can accept up to (2) 1 1/4" trade size PVC conduit feeds. Boxes are designed to be installed separately or ganged together, for greater capacity and flexibility. They work with XB814 cover assemblies (sold separately).

Features & Benefits

cUL Coming Soon

UL listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use – Tested and listed by Underwriters Laboratories, Inc. to UL2996 and UL50E for use in the ground in all weather conditions.

Outdoor-Rated Construction – UV and chemical-resistant F1 rated nonmetallic materials, allows the box to hold up for years to come.

Modular design – Boxes are designed to interlock allowing endless number of boxes in the same location. Provides service separation, everything in one location, and easier installation.

Air Pocket Design – This innovative design traps and maintains an air pocket protecting the devices, plugs and connections from water, snow, and ice. Allow for safer operation year round.

ADA Compliant – Meets all specifications for ADA guidelines.

Holds up to 5000 lbs – Has an ANSI/SCTE 77 Tier 5 rating and can hold up to 5,000 lbs of load allowing for the occasional tractor or non-deliberate vehicular traffic.

Flush to the Finished Ground – Designed to be flush with any surface, grass, dirt, walkways, patios, etc.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776187182
Country Of Origin	China	Construction	Assembled
Number of Knockouts	0	Application Sector	Commercial
Standard	UL Listed Outdoor In-Ground Boxes: File E486738 Guide QCNL.	Type	Ground Box

Dimensions

Product Width US	8.125 in	Product Height US	10.75 in
Product Length US	16.125 in	Cubic Capacity	123 cu in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E486738	cULus Listed	Yes
Additional Information			
RoHS Conformant	Yes	Product Environmental Profile	Yes