



Outdoor charging station with an LED accent light to enable device charging during the day and after dark. Accent light ensures the station stands out from standard bollards and clearly indicates charging. The station includes two 4-Port USB Outlets.

## Features & Benefits

- Charging & Illumination - Combine power with area lighting in one pedestal to maximize functionality of outdoor spaces.

Outdoor-Rated Construction - Rugged aluminum form designed for durability in all weather conditions. UL listed to NEMA 3R requirements to ensure optimal performance.
- Durable, Premium Finishes - Available in three outdoor-rated finishes to complement your space design. Choose from black, bronze or silver.

A/V & Communication Compatible - Add an A/V-Communication Kit to 3-gang versions to accommodate Wiremold AVIP plates as well as decorator A/V or communication devices. Enables pedestal to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.
- Device Shelves - Add up to two pairs of shelves to hold mobile devices while charging.

Door Options - Interior illuminates when door is open. Replace standard color-matched door with a transparent version to make devices inside more visible. Or, select a lockable door for added security or to ensure use is limited to facility personnel.

## Specifications

### General Info

Product Line	Wiremold	Color	Black
UPC Number	786776185843	Country Of Origin	Mexico
Features	USB-A Charging	Application Sector	Commercial
Standard	cULus Listed, File Number E479489, Guide PUPR	Type	Charging Stations
Installed Devices	4-Port USB-A		

### Dimensions

Product Width US	6.0 in	Product Weight US	6.0 lb
Product Height US	46.5 in	Product Length US	8.0 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E479489	cULus Listed	Yes
Buy American Act Compliance			
NAFTA	Yes		
Additional Information			
RoHS Conformant	Yes	Product Environmental Profile	Yes
Technical Information			
Is Pre-Wired	Yes	Number of USBs	8
Number of Gangs	2	Lighting Types	Accent Light