



Wiremold
Charging Station with Area Light, 3-Gang, (1) Duplex GFCI, (2) 4-Port USB-A Outlets - Silver
Part No. XCSLF3GRUU-SV



Charging Station with Area Light is a charging station with an LED light to eliminate the need for a stand-alone bollard. Perfect for use as pathway lighting in educational, corporate and recreational applications.

Features & Benefits

Combine power with area lighting in one pedestal to maximize functionality of outdoor spaces.

Outdoor-Rated Construction – Rugged aluminum form designed for durability in all weather conditions. UL listed to NEMA 3R requirements to ensure optimal performance.

Durable, Premium Finishes – Available in three outdoor-rated finishes to complement your space design. Choose from black, bronze or silver.

Add an A/V-Communication Kit to 3-gang versions to accommodate Wiremold AVIP plates as well as decorator A/V or communication devices.

Add up to two pairs of shelves to hold mobile devices while charging

Interior illuminates when door is open. Replace standard color-matched door with a transparent version to make devices inside more visible. Or, select a lockable door for added security or to ensure use is limited to facility personnel.

Enables pedestal to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.

Specifications

General Info

Product Line	Wiremold	Color	Silver
UPC Number	786776186161	Country Of Origin	Mexico
Number of Receptacles	1	Features	USB-A Charging
Application Sector	Commercial	Standard	cULus Listed, File Number E479489, Guide PUPR
Type	Charging Stations	Installed Devices	4-Port USB-A, GFCI

Dimensions

Product Width US	6.0 in	Product Weight US	43.0 lb
Product Height US	48.0 in	Product Length US	8.0 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E479489	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Is Pre-Wired	Yes	Number of USBs	8
Number of Gangs	3	Amperage	20 A
Lumens	457 lm	Lighting Types	Area Light