



**Wiremold**  
**Outdoor Rooftop Box, Unwired, Black Cover**  
Part No. XFB2GBK



The Outdoor Rooftop Box is an innovative solution that provides convenient access to power on raised rooftop deck environments. Install power access anywhere along a deck's surface. This rooftop box is perfect for outdoor events or furniture requiring access to power, eliminating the need for extension cords along the decking surface and providing greater flexibility in power distribution on rooftops. The box is designed to be installed flush alongside rooftop pavers and features a hinged top self-closing cover. The internal rotating outlet box can be rotated upwards when power access is needed and rotates downward when in-use. The rooftop box supports (2) 20A weather-resistant, GFCI duplex receptacles. The prewired unit comes with receptacles pre-installed and wire leads for wiring up to nearby junction boxes.

## Features & Benefits

**Easy Installation:** The outdoor rooftop box is designed to integrate seamlessly into raised floor patio systems commonly used on rooftops.

**Shallow Design:** Can be used in any raised floor system with 7" or more of space from top of floor to roof surface.

**1000Lb Load Rating:** Capable of withstanding loads of 1000lbs, this box can handle loads from foot traffic, drink carts or dollies suppling the outdoor area.

**Match Space Aesthetic:** Available in both gray and black cover finishes to complement rooftop decking.

**Flush, Durable Design:** The outdoor rooftop box sits flush with the floor and incorporates a slip resistant surface to prevent safety issues.

**While-in-Use Design:** Plug in your devices, route cables through egress and close the cover for NEMA 3R protection while in use.

**Self-Closing Cover:** Self-closing to prevent users from leaving the receptacles exposed to the elements and open cover tripping hazards.

**2-Gangs of Capacity:** Unwired unit provides 2-gangs of capacity. Prewired unit includes two 20A duplex weather-resistant GFCI outlets.

## Specifications

### General Info

Product Line	Wiremold	Color	Black
UPC Number	786776198652	Country Of Origin	China
Conduit Size	1/2 in	Installation Location	Rooftop Pavers
Application Sector	Commercial, Hospitality, Multi-Dwelling Unit	Warranty Type	1-Year from Installation or 2-Years from Day of Sale

### Dimensions

Product Width US	8.0 in	Product Weight US	6.1 lb
Product Height US	6.25 in	Product Length US	11.75 in

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	-22 °F	Is Pre-Wired	No
Service Capacity	Single	Floor Thickness Supported	0.75 to 2.25 in
Operating Temperature Max	122 °F	Number of Gangs	2
Enclosure Type	NEMA 3R	Load Capacity	1000 lb
Number of Channels	1	Operating Temperature	-22°F-122°F
Relative Humidity	Up to 95% Non-condensing	Maximum Amperage Supported	20 A