WALL-MOUNT CABINET SPECIFICATION GUIDE

VERTICAL WALL-MOUNTS

VWMSD-4RU-36-B

VWMFD-4RU-36-B

MODEL NUMBER	USABLE RACK SPACE (RU)	ADDITIONAL USABLE RU*	FEATURES	LOAD RATING UL2416 (lbs)	MAXIMUM EQUIPMENT DEPTH	UNIT DIMENSIONS	UNIT WEIGHT (lbs)	SHIPPING DIMENSIONS	SHIPPING WEIGHT (lbs)	EIA RAIL TYPE (REVERSIBLE)	CERTIFICATIONS	WARRANTY
VWMSD-4RU-36-B	4RU	4RU	Split Door Narrow Depth	150lbs	31"	12"D x 25"W x 36"H	71lbs	15.5"D x 29.0"W x 39.5"H	81lbs	3/8" sqr. & 12-24	UL2416, EIA-310-E, PCI, & TAA	5 yrs
VWMSD-4RU-42-B	4RU	4RU	Split Door Narrow Depth Extended Height	150lbs	37"	12"D x 25"W x 42"H	79lbs	15.5"D x 29.0"W x 45.5"H	89lbs	3/8" sqr. & 12-24	UL2416, EIA-310-E, PCI, & TAA	5 yrs
VWMSD-8RU-36-B	8RU	8RU	Split Door Medium Depth	150lbs	31"	18"D x 25"W x 36"H	84lbs	21.5"D x 29.0"W x 39.5"H	94lbs	3/8" sqr. & 12-24	UL2416, EIA-310-E, PCI, & TAA	5 yrs
VWMSD-8RU-42-B	8RU	8RU	Split Door Medium Depth Extended Height	150lbs	37"	18"D x 25"W x 42"H	95lbs	21.5"D x 29.0"W x 45.5"H	105lbs	3/8" sqr. & 12-24	UL2416, EIA-310-E, PCI, & TAA	5 yrs
VWMFD-4RU-36-B	4RU	4RU	Full Door Narrow Depth	150lbs	31"	12"D x 25"W x 36"H	71lbs	15.5"D x 29.0"W x 39.5"H	81lbs	3/8" sqr. & 12-24	UL2416, EIA-310-E, PCI, & TAA	5 yrs
VWMFD-8RU-36-B	8RU	8RU	Full Door Medium Depth	150lbs	31"	18"D x 25"W x 36"H	79lbs	21.5"D x 29.0"W x 39.5"H	89lbs	3/8" sqr. & 12-24	UL2416, EIA-310-E, PCI, & TAA	5 yrs

*Usable additional RU space requires optional brackets

SWING-OUT WALL-MOUNTS

SWM12RUPL-26-26

SWM18RUPD-26-26

SWM26RUSD-26-26

MODEL NUMBER	USABLE RACK SPACE (RU)	ADDITIONAL USABLE RU* REAR PAN	FEATURES	LOAD RATING UL2416 (lbs)	MAXIMUM EQUIPMENT DEPTH	UNIT DIMENSIONS	UNIT WEIGHT (lbs)	SHIPPING DIMENSIONS	SHIPPING WEIGHT (lbs)	EIA RAIL TYPE	CERTIFICATIONS	WARRANTY
SWM12RUSD-26-26	12RU	2RU	Solid Door	125 lbs	23.5"	28"D x 26"W x 25"H	89lbs	30.5"D x 29.5"W x 30.5"H	110lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs
SWM12RUPL-26-26	12RU	2RU	Plexiglass door	125 lbs	23.5"	28"D x 26"W x 25"H	89lbs	30.5"D x 29.5"W x 30.5"H	110lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs
SWM12RUPD-26-26	12RU	2RU	Perforated door	125 lbs	23.5"	28"D x 26"W x 25"H	89lbs	30.5"D x 29.5"W x 30.5"H	110lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs
SWM18RUSD-26-26	18RU	2RU	Solid Door	150 lbs	23.5"	28"D x 26"W x 35.4"H	114lbs	30.5"D x 29.5"W x 41.0"H	135lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs
SWM18RUPL-26-26	18RU	2RU	Plexiglass door	150 lbs	23.5"	28"D x 26"W x 35.4"H	114lbs	30.5"D x 29.5"W x 41.0"H	135lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs
SWM18RUPD-26-26	18RU	2RU	Perforated door	150 lbs	23.5"	28"D x 26"W x 35.4"H	114lbs	30.5"D x 29.5"W x 41.0"H	135lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs
SWM26RUSD-26-26	26RU	2RU	Solid Door	200 lbs	23.5"	28"D x 26"W x 49.4"H	139lbs	30.5"D x 29.5"W x 54.5"H	160lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs
SWM26RUPL-26-26	26RU	2RU	Plexiglass door	200 lbs	23.5"	28"D x 26"W x 49.4"H	139lbs	30.5"D x 29.5"W x 54.5"H	160lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs
SWM26RUPD-26-26	26RU	2RU	Perforated door	200 lbs	23.5"	28"D x 26"W x 49.4"H	139lbs	30.5"D x 29.5"W x 54.5"H	160lbs	12-24 threaded	UL2416, EIA-310-E, PCI, & TAA	5 yrs

*Usable additional RU space requires optional brackets

©2023 Legrand All Rights Reserved LIT#1992