SWING-OUT WALL- MOUNT CABINETS

The SWM Series wall-mount cabinets provide a convenient and easy-to-use solution for Edge, IoT, PoE and small network applications. The small form factor cabinets are 28" deep for medium to large network equipment. The SWM cabinets are made of rugged welded steel complete with locking doors to support PCI applications. The hinged, swing-out middle section provides easy access to the rear of mounted equipment. The SWM series is perfect for secure networks, small data closets, retail, educational, edge computing, and all areas where floor space is at a premium.

Solid Front Door

Perforated Front Door

Plexiglass Front Door



- Full swing handle enables future lock upgrades
- Reversible hinged front locking door
- Secure for PCI applications

- Vented sides with mounting locations for optional cooling fans
- 12-24 threaded mounting holes
- Solid top protects equipment from spills and leaks

- Cable knockouts at top and bottom of fixed rear pan for cable egress
- Large cutout in rear pan for wall cable egress

Certified load ratings per UL2416

12RU Cabinet - 125lbs capacity
18RU Cabinet - 150lbs capacity
26RU Cabinet - 200lbs capacity

BENEFITS:

- ✔ Space-saving design
- ✔ Swing-out design allows easy access to front and rear of equipment
- ✔ Depth accepts equipment up to 23.5" deep
- ✔ Locking panels for secure applications
- ✔ Rugged welded frame construction for increased load capacity
- ✔ Versitile for small data room applications
- ✔ Create a self-contained data closet
- ✔ Ships fully assembled

CABINETS INCLUDE:

- ✔ 2 front mounting rails
- ✔ 2 door lock keys
- ✔ 8 cable management rings
- ✔ Owner's manual

CABINETS

PART NO.	HEIGHT	DOOR TYPE	DESCRIPTION
SWM12RUSD-26-26	25"	Solid	Swing-out cabinet, 12RU, solid door
SWM12RUPL-26-26	25"	Plexiglass	Swing-out cabinet, 12RU, plexiglass door
SWM12RUPD-26-26	25"	Perforated	Swing-out cabinet, 12RU, perforated door
SWM18RUSD-26-26	35.5"	Solid	Swing-out cabinet, 18RU, solid door
SWM18RUPL-26-26	35.5"	Plexiglass	Swing-out cabinet, 18RU, plexiglass door
SWM18RUPD-26-26	35.5"	Perforated	Swing-out cabinet, 18RU, perforated door
SWM26RUSD-26-26	49.5"	Solid	Swing-out cabinet, 26RU, solid door
SWM26RUPL-26-26	49.5"	Plexiglass	Swing-out cabinet, 26RU, plexiglass door
SWM26RUPD-26-26	49.5"	Perforated	Swing-out cabinet, 26RU, perforated door

RAIL ACCESSORIES

PART NO.	DESCRIPTION	USED WITH CABINET
SWMRK12RU	Vertical rail kit, 12RU, 12-24 threaded holes	SWM12RUXX-26-26
SWMRK18RU	Vertical rail kit, 18RU, 12-24 threaded holes	SWM18RUXX-26-26
SWMRK26RU	Vertical rail kit, 26RU, 12-24 threaded holes	SWM26RUXX-26-26

ACCESSORIES

PART NO.	DESCRIPTION
SWMPDU12RU	PDU mounting kit, 12RU
SWMPDU18RU	PDU mounting kit, 18RU
SWMPDU26RU	PDU mounting kit, 26RU
SWMVFK12RU	Cable management kit, 12RU, qty 2 rails
SWMVFK18RU	Cable management kit, 18RU, qty 2 rails
SWMVFK26RU	Cable management kit, 26RU, qty 2 rails
SWMFSK	Fiber spool mounting kit
SWMHMBM12	Horizontal mounting bracket kit, 2RU

ACCESSORY FEATURES

1 19" mounting rail kit
- Allows for rear mounting of equipment
- Addition to rear of enclosure provides 4 point attachment for larger equipment
- Adjustable front to rear
- 12-24 threaded mounting holes

2 Vertical PDU mount bracket kit
- Mount industry standard PDU to either side of the cabinet
- PDU mounts rear facing to provide clearance for rack mounted equipment

3 Verical cable management
- Mount to existing front 19" mounting rails
- Manage cables with cable management fingers at each RU increment
- Large capacity, 4" depth

4 Fiber spool mounting kit
- Snap fits to rear pan
- Creates a dual fiber spool location to take up fiber slack

5 Horizontal mounting bracket kit
- Snap fits to rear pan
- Allows an additional 2RU of vertically mounted 19" rack mount equipment on the rear pan

1



2

3



4



5