

# Mighty Mac™ Behavioral Health Wall Plates

## Minimize Risk. Maximize Safety.

Legrand's Mighty Mac Behavioral Health Wall Plates combine advanced safety features with sleek, modern design to create a secure, supportive environment in behavioral health applications and correctional facilities.

With ligature-resistant design, tamper-resistant construction and robust durability, these wall plates minimize attachment points while seamlessly integrating into the aesthetic of a space, offering a solution that prioritizes patient safety without compromising on style or functionality.



### Ligature-Resistant Design

Minimizes attachment points for enhanced safety.

### Tamper-Resistant Construction

Prevents tampering and removal.

### Durable, Impact-Resistant Materials

Built to withstand demanding environments  
(passes 1000-hour salt spray test) .

### Safety Without Sacrificing Style

Sleek, modern aesthetic. Available in Cold Rolled Steel or Brushed Stainless Steel finishes. Painted options available in White or Ivory.

### Variety of Configurations

Decorator, Duplex, Toggle Switch, Round Receptacle, Blank.

### Multiple Size Variants

One gang, two gang or three gang.

### Thickness Options

10 gauge, 14 gauge.

### Ground Wire Lead on Backplate for Compliance to UL 514D and NFPA 70

Paint removed from wall plate screw opening and a subframe ground wire lead for added protection and adequate bonding.

# Mighty Mac™ Behavioral Health Wall Plates

## Ordering Information (Ex: WPPA1N911IVYPS)

MODEL	MATERIAL	GANG SIZE	DEVICES	WALL PLATE STYLE	FASTENERS	OPTION	MANUFACTURER
<b>WPP</b>	<b>A</b>	<b>1</b>	<b>N</b>	<b>91</b>	<b>1</b>	<b>IVY</b>	<b>PS</b>

### MODEL

**WSP** Wall Surface Mount Plate

**WPP** Wall Pour-in-Place Plate

### MATERIAL

**A** 10-Ga CRS (Painted)

**0** 14-Ga CRS (Painted)

**3** 14-Ga SS (Painted)

**6** 14-Ga SS (Brushed)

### GANG SIZE

**1** Single Gang (1 Device Max.)

**2** Double Gang (2 Devices Max.)

**3** Triple Gang (3 Devices Max.)

### DEVICES

**B** Blank

**D** Duplex Opening

**G** Decorator Opening

**N\*** Single Round Receptacle

**S** Switch (Toggle)

*\*When selecting an N to add 91 from wall plate style*

### WALL PLATE STYLE

**91** 1.5938 hole for 1.5625 dia. device

### FASTENERS

**1** Torx® T-20 Hoad w/Center Pin

**2** Allen Head w/ Center Pin

### OPTION

(Leave blank for standard white or brushed finish)

**IVY** Ivory Color

### MANUFACTURER

**PS** Pass & Seymour®

### ACCESSORIES FOR ORDER

**D0418PS** Torx® Screwdriver

**D0377PS** Allen Head Screwdriver

