NOTES: UNLESS OTHERWISE SPECIFIED

1. OPTICAL PERFORMANCE SHALL BE IN ACCORDANCE PER SPECIFICATION #71800061C. THE TIER LEVELS ARE SHOWN IN TABLE 2.
2. THE "G" SUFFIX IN THE PART NUMBER DESIGNATES THE FIBER TYPE. SEE TABLE 2.
3. FIBER TYPE, PIGTAIL TYPE IDENTIFIER & PERFORMANCE TIER LEVEL("GXY"): CONFIGURATION AS DEFINED IN TABLES 2, 3.
4. THE CASSETTE HOUSING IS PLASTIC.
5. PIGTAIL PORT ID LABEL WILL HAVE THE FOLLOWING TEXT ("XX" & "ZZ" ARE DERIVED FROM TABLE 4)
   "DD EE/125 24F"
6. ALL DIMENSIONS ARE IN INCHES.
7. US PATENT NUMBERS 8,398,039; 10,591,682; & 10,788,640.
8. FOR RIBBON FIBER CONFIGURATIONS, THE INTERNAL HARNESS FIBER SHALL HAVE 900um BUFFER TUBE COLOR CODED TO MATCH THE UNDERLYING FIBER COLOR PER TABLE 5.
9. LLL IS THE LENGTH OF THE PIGTAIL. M IS THE UNIT OF MEASURE, EITHER 'M' FOR METERS OR 'F' FOR FEET, THE LENGTH TOLERANCE FOR THE PIGTAIL SHALL BE -.00/+.12 METERS.

⬡ DENOTES NOTE REFERENCE



ISOMETRIC VIEW

TABLE 1	
"BB"	FRONT PNL ADAPTER
LA	LC (APC)
LC	LC (UPC)

TABLE 2			
"G"	TYPE	"Y"	TIER
H	MM 50/125 (OM4)	1	1
J	SM 9/125 (OS2)	1	1
W	MM 50/125 (OM5)	1	1

TABLE 3	
"X"	"TYPE"
P	PIGTAIL 250UM RIBBON
T	PIGTAIL 900UM TIGHT BUFFER
U	PIGTAIL 250UM MICRO ARRAY LOOSE TUBE

TABLE 4		
"G"	"DD"	"EE"
H	MM	50
J	SM	9
W	MM	50

TABLE 5	
FIBER COLOR BY PORT	
PORT #**	FIBER COLOR
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
5	SLATE
6	WHITE
7	RED
8	BLACK
9	YELLOW
10	VIOLET
11	ROSE
12	AQUA
13	BLUE
14	ORANGE
15	GREEN
16	BROWN
17	SLATE
18	WHITE
19	RED
20	BLACK
21	YELLOW
22	VIOLET
23	ROSE
24	AQUA

** LC PORT NUMBERING:
PER FRONT PANEL MARKING





SIDE VIEW



REAR VIEW
24F, (1) PIGTAIL CASSETTE

LM4-BBQ24G-ZXYLLLM

BASE NUMBER
FRONT ADAPTER TYPE (TABLE 1)
NUMBER OF FIBERS
FIBER TYPE & BANDWIDTH IDENTIFIER (USE TABLE 2)
PIGTAIL IDENTIFIER
PIGTIAL TYPE (USE TABLE 3)
PERFORMANCE TIER LEVEL IDENTIFIER (USE TABLE 2)
LENGTH AND UNIT OF MEASURE

PART NUMBER LEGEND

*** NOTICE ***
THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF LEGRAND INC.

legrand® WWW.LEGRAND.US

TITLE: CASS, M4, 24, LC, QD, PIGTAIL

	NAME	DATE
DWN	LWJ	12/03/2024
CHK	XQZ	12/2/2024
APPR		

SIZE	CAD FILE	DWG NO	REV
C	LM4BBQ24GZXYLLLMC	LM4-BBQ24G-ZXYLLLM	00

SCALE 1:2 SHEET 1 OF 1