Metal Flat Cover Mounting Screw
Self Tap #10-32 x 1.0”



.030	.090	.188	.118	.448	1.000	16	10(.190)
"F"	"E"	"D"	"C"	"B"	"A"	TPI	THREAD SIZE

Metal Flat Cover Lock Washer
External Teeth #10



.020	.025	.395	.406	.195	.204	10
MIN	MAX	MIN	MAX	MIN	MAX	SCREW SIZE NOMINAL
"C" THICKNESS		"B" OUTSIDE DIAMETER		"A" INSIDE DIAMETER		

Metal Hinged Door Mounting Screw
Self Tap #6-32 x 0.375”



.375	6-32UNC-2A	.270	.141	.135	.097	.175	.035
L	THD SIZE	B MAX	C MAX	D MAX	H MAX	M MAX	N MIN

Metal Hinged Door Lock Washer
External Teeth #6



.016	.022	.305	.317	.142	.150	6
MIN	MAX	MIN	MAX	MIN	MAX	SCREW SIZE NOMINAL
"C" THICKNESS		"B" OUTSIDE DIAMETER		"A" INSIDE DIAMETER		