PASS & SEYMOUR®

PLUGS & CONNECTORS

# READY-TO-WIRE SOLUTIONS THAT REALLY WORK

designed to be better.™

legrand®

2
11
22
20
14
BIGJOE
BIGJOE
BIGJOE

# Rugged, reliable and
# READY FOR ACTION.

**Look at our complete line** of quality Plugs & Connectors, and you'll see durability and productivity everywhere. In our choice of premium materials. In robust, uncompromising construction. And, most of all, in superior, innovative designs based on decades of feedback from contractors and MRO professionals. Pass & Seymour Plugs & Connectors are built to work for you — offering years of dependable service in the toughest real-world conditions and delivering maximum productivity on the jobsite. **See for yourself.**

## Turnlok®
## Locking Devices

Work for you by installing 3x faster with quick-thread assembly screws. Built tough for all types of industrial applications.

## Pass & Seymour
## Straight Blade Devices

More safety and productivity on the job with quick, intuitive wiring and a recessed cord grip to reduce screwdriver slippage.

## Pass & Seymour
## Pin & Sleeve Devices

IEC 309 solutions provide reliable protection from moisture and contaminants, and are completely ready to wire for quick, simple installation.

Demand Turnlok® locking devices

# FOR DEMANDING INDUSTRIAL APPLICATIONS.

**Raised ribs** provide non-slip gripping profile for locking and unlocking.

**Double dovetail design** provides superior protection against cord pull-out forces.

**Industrial-strength, brass alloy plug blades** and connector contacts resist heat rise, provide excellent conductivity.

**Scallop shell design** provides non-slip gripping surface for insertion and withdrawal.

**Quick-thread assembly screws** install 3x faster and cord-grip screws come backed out, ready to wire.

**L630C, L630P**

**New-design external cord grips** provide visible assurance of safe and proper cord retention.

## Industrial Spec Grade Angle Plugs & Adapters

- Angle plugs and adapters both allow for 4-position face rotation
- 20/30A 3 Wire Turnlok® Right Angle Adapters are adjustable up to 8 positions

**PS4720SSAN**

## Heavy-Duty Turnlok® Ground Continuity Monitoring (GCM) Plugs & Connectors

- Continuous monitoring devices enhance personal safety and add convenience on the job
- Dual, bright LED indicators with 360-degree visibility
- Exclusive neoprene dust shield seals devices and protects against contaminants

**L630CGCM, L630PGCM**

### Green LED

**Plug** – There's proper ground continuity from the panel to the outlet and power is present.

**Connector** – Power is present, and there's proper ground continuity throughout the cordset and back to the panel.

### Red LED

**Plug** – Power is present, but there's a ground continuity fault or miswire between the receptacle and the panel.

**Connector** – Power is present, but there's a ground continuity fault or miswire in the cordset (or, if there's a red indication in the plug as well, between the receptacle and the panel). It's also possible there could be a problem in both.

### No LED

**Plug** – Power loss, open hot or neutral conductor, or hot/ground reversal.

**Connector** – Assuming power is present at the outlet, there's an open hot or open neutral conductor in the cordset, or a hot/ground reversal.

*250V products will show red and green when hot and ground are reversed.*

## Rubber & Watertight Plugs & Connectors

- Rubber body construction stands up to impacts, oil, chemicals, heat, and weather
- Floating blades allow self-alignment with contacts and reduce stress on blades and contacts

**25W47, 2547**

## California Standard & Corrosion-Resistant

- Designed to meet California electrical requirements

**CS8264, CS8165**

# Turnlok® Plugs & Connectors

**IP20**
Suitability

L520C

L620P

L920C

L530P

L630C

L830P

L1020P

L1030C

| CATALOG NUMBER | GCM CATALOG NUMBER | RATING A. | RATING V. | DESCRIPTION/COLOR | NEMA CONFIG. NO. | 3RD PARTY COMPLIANCE UL 498 | FSUL WC596 | CSA |
|---|---|---|---|---|---|---|---|---|
| **20 Amp NEMA L520 2 Pole, 3 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L520C** | **L520CGCM** | 20 | 125 | Connector, Black Back, White Front Body | L5-20R | • | • | • |
| **CRL520C** | | 20 | 125 | Connector, Yellow Back, White Front Body, Corr.-Resist. | L5-20R | • | • | • |
| **L520P** | **L520PGCM** | 20 | 125 | Plug, Black Back, White Front Body | L5-20P | • | • | • |
| **20 Amp NEMA L620 & L720 2 Pole, 3 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L620C** | **L620CGCM** | 20 | 250 | Connector, Black Back, White Front Body | L6-20R | • | • | • |
| **CRL620C** | | 20 | 250 | Connector, Yellow Back, White Front Body, Corr.-Resist. | L6-20R | • | • | • |
| **L720C** | **L720CGCM** | 20 | 277* | Connector, Black Back, White Front Body | L7-20R | • | • | • |
| **L620P** | **L620PGCM** | 20 | 250 | Plug, Black Back, White Front Body | L6-20P | • | • | • |
| **CRL620P** | | 20 | 250 | Plug, Yellow Back, White Front Body, Corr.-Resist. | L6-20P | • | • | • |
| **L720P** | **L720PGCM** | 20 | 277* | Plug, Black Back, White Front Body | L7-20P | • | • | • |
| **20 Amp NEMA L820, L920 , L3720 & L2420 2 Pole, 3 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L820C** | | 20 | 480 | Connector, Black Back, White Front Body | L8-20R | • | | • |
| **L920C** | | 20 | 600 | Connector, Black Back, White Front Body | L9-20R | • | | • |
| **L3720C** | **L3720CGCM** | 20 | 347 | Connector, Black Back, White Front Body | L24-20R | | | • |
| **L820P** | | 20 | 480 | Plug, Black Back, White Front Body | L8-20P | • | | • |
| **L920P** | | 20 | 600 | Plug, Black Back, White Front Body | L9-20P | • | | • |
| **L3720P** | **L3720PGCM** | 20 | 347 | Plug, Black Back, White Front Body | L24-20P | • | • | • |
| **30 Amp NEMA L530 2 Pole, 3 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L530C** | **L530CGCM** | 30 | 125 | Connector, Black Back, White Front Body | L5-30R | • | • | • |
| **CRL530C** | | 30 | 125 | Connector, Yellow Back, White Front Body, Corr.-Resist. | L5-30R | • | • | • |
| **L530P** | **L530PGCM** | 30 | 125 | Plug, Black Back, White Front Body | L5-30P | • | • | • |
| **CRL530P** | | 30 | 125 | Plug, Yellow Back, White Front Body, Corr.-Resist. | L5-30P | • | • | • |
| **30 Amp NEMA L630 & L730 2 Pole, 3 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L630C** | **L630CGCM** | 30 | 250 | Connector, Black Back, White Front Body | L6-30R | • | • | • |
| **CRL630C** | | 30 | 250 | Connector, Yellow Back, White Front Body, Corr.-Resist. | L6-30R | • | • | • |
| **L730C** | **L730CGCM** | 30 | 277* | Connector, Black Back, White Front Body | L7-30R | • | • | • |
| **L630P** | **L630PGCM** | 30 | 250 | Plug, Black Back, White Front Body | L6-30P | • | • | • |
| **CRL630P** | | 30 | 250 | Plug, Yellow Back, White Front Body, Corr.-Resist. | L6-30P | • | • | • |
| **L730P** | **L730PGCM** | 30 | 277* | Plug, Black Back, White Front Body | L7-30P | • | • | • |
| **30 Amp NEMA L830 & L930 2 Pole, 3 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L830C** | | 30 | 480 | Connector, Black Back, White Front Body | L8-30R | • | • | • |
| **L930C** | | 30 | 600 | Connector, Black Back, White Front Body | L9-30R | • | • | • |
| **L830P** | | 30 | 480 | Plug, Black Back, White Front Body | L8-30P | • | • | • |
| **L930P** | | 30 | 600 | Plug, Black Back, White Front Body | L9-30P | • | • | • |
| **20 Amp NEMA L1020, L1120 & L1220 3 Pole, 3 Wire Non-Grounding** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L1020C** | | 20 | 125/250 | Connector, Black Back, White Front Body | L10-20R | • | • | • |
| **L1120C** | | 20 | 3Ø,250 | Connector, Black Back, White Front Body | L11-20R | • | • | • |
| **L1220C** | | 20 | 3Ø,480 | Connector, Black Back, White Front Body | L12-20R | • | • | • |
| **L1020P** | | 20 | 125/250 | Plug, Black Back, White Front Body | L10-20P | • | • | • |
| **L1120P** | | 20 | 3Ø,250 | Plug, Black Back, White Front Body | L11-20P | • | • | • |
| **L1220P** | | 20 | 3Ø,480 | Plug, Black Back, White Front Body | L12-20P | • | • | • |
| **30 Amp NEMA L1030, L1130, L1230 & L1330 3 Pole, 3 Wire Non-Grounding** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L1030C** | | 30 | 125/250 | Connector, Black Back, White Front Body | L10-30R | • | • | |
| **L1130C** | | 30 | 3Ø,250 | Connector, Black Back, White Front Body | L11-30R | • | • | • |
| **L1230C** | | 30 | 3Ø,480 | Connector, Black Back, White Front Body | L12-30R | • | • | • |
| **L1330C** | | 30 | 3Ø,600 | Connector, Black Back, White Front Body | L13-30R | • | • | • |
| **L1030P** | | 30 | 125/250 | Plug, Black Back, White Front Body | L10-30P | • | • | |
| **L1130P** | | 30 | 3Ø,250 | Plug, Black Back, White Front Body | L11-30P | • | • | • |
| **L1230P** | | 30 | 3Ø,480 | Plug, Black Back, White Front Body | L12-30P | • | • | • |
| **L1330P** | | 30 | 3Ø,600 | Plug, Black Back, White Front Body | L13-30P | • | • | • |

# Turnlok® Plugs & Connectors

**IP20**
Suitability

CRL1420C

L1430P

L1630P

CS8464

CS8165

| CATALOG NUMBER | GCM CATALOG NUMBER | RATING A. | RATING V. | DESCRIPTION/COLOR | NEMA CONFIG. NO. | 3RD PARTY COMPLIANCE UL 498 | FSUL WC596 | CSA |
|---|---|---|---|---|---|---|---|---|
| **20 Amp NEMA L1420, L1520 & L1620 3 Pole, 4 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L1420C** | **L1420CGCM** | 20 | 125/250 | Connector, Black Back, White Front Body | L14-20R | • | • | • |
| **CRL1420C** | | 20 | 125/250 | Connector, Yellow Back, White Front Body, Corr.-Resist. | L14-20R | • | • | • |
| **L1520C** | | 20 | 3Ø,250 | Connector, Black Back, White Front Body | L15-20R | • | • | • |
| **L1620C** | | 20 | 3Ø,480 | Connector, Black Back, White Front Body | L16-20R | • | • | • |
| **L1420P** | **L1420PGCM** | 20 | 125/250 | Plug, Black Back, White Front Body | L14-20P | • | • | • |
| **CRL1420P** | | 20 | 125/250 | Plug, Yellow Back, White Front Body, Corr.-Resist. | L14-20P | • | • | • |
| **L1520P** | | 20 | 3Ø,250 | Plug, Black Back, White Front Body | L15-20P | • | • | • |
| **L1620P** | | 20 | 3Ø,480 | Plug, Black Back, White Front Body | L16-20P | • | • | • |
| **30 Amp NEMA L1430 & L1530 3 Pole, 4 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L1430C** | **L1430CGCM** | 30 | 125/250 | Connector, Black Back, White Front Body | L14-30R | • | • | • |
| **CRL1430C** | | 30 | 125/250 | Connector, Yellow Back, White Front Body, Corr.-Resist. | L14-30R | • | • | • |
| **L1530C** | | 30 | 3Ø,250 | Connector, Black Back, White Front Body | L15-30R | • | • | • |
| **L1430P** | **L1430PGCM** | 30 | 125/250 | Plug, Black Back, White Front Body | L14-30P | • | • | • |
| **CRL1430P** | | 30 | 125/250 | Plug, Yellow Back, White Front Body, Corr.-Resist. | L14-30P | • | • | • |
| **L1530P** | | 30 | 3Ø,250 | Plug, Black Back, White Front Body | L15-30P | • | • | • |
| **30 Amp NEMA L1630 & L1730 3 Pole, 4 Wire** (Cord Diameter .225" – 1.150") | | | | | | | | |
| **L1630C** | | 30 | 3Ø,480 | Connector, Black Back, White Front Body | L16-30R | • | • | • |
| **L1730C** | | 30 | 3Ø,600 | Connector, Black Back, White Front Body | L17-30R | • | • | • |
| **L1630P** | | 30 | 3Ø,480 | Plug, Black Back, White Front Body | L16-30P | • | • | • |
| **L1730P** | | 30 | 3Ø,600 | Plug, Black Back, White Front Body | L17-30P | • | • | • |
| **California Standard & Corrosion-Resistant, 3 Wire Grounding** (Cord Diameter .680" – 1.125") | | | | | | | | |
| **CR6360** | | 50 | 125 | Connector, Corrosion-Resistant | | • | | • |
| **CS6360** | | 50 | 125 | Connector, California Standard | | • | | • |
| **CS8264** | | 50 | 250 | Connector, California Standard | | • | | • |
| **CS8464** | | 50 | 480 | Connector, California Standard | | • | | • |
| **3762** | | 50 | 250VDC. 600VAC | Connector, Corrosion-Resistant | | • | | • |
| **CR6361** | | 50 | 125 | Plug, Corrosion-Resistant | | • | | • |
| **CS6361** | | 50 | 125 | Plug, California Standard | | • | | • |
| **CS8265** | | 50 | 250 | Plug, California Standard | | • | | • |
| **CS8465** | | 50 | 480 | Plug, California Standard | | • | | • |
| **3763M** | | 50 | 250VDC. 600VAC | Plug, Corrosion-Resistant | | • | | • |
| **California Standard & Corrosion-Resistant, 4 Wire Grounding** (Cord Diameter .680" – 1.125") | | | | | | | | |
| **CR6364** | | 50 | 125/250 | Connector, Corrosion-Resistant | | • | | • |
| **CS6364** | | 50 | 125/250 | Connector, California Standard | | • | | • |
| **CS8364** | | 50 | 3Ø,250 | Connector, California Standard | | • | | • |
| **CS8164** | | 50 | 3Ø,480 | Connector, California Standard | | • | | • |
| **3764** | | 50 | 250VDC. 600VAC | Connector, Corrosion-Resistant | | • | | • |
| **7764**** | | 50 | 250VDC. 600VAC | Connector, Corrosion-Resistant | | • | | • |
| **CR6365** | | 50 | 125/250 | Plug, Corrosion-Resistant | | • | | • |
| **CS6365** | | 50 | 125/250 | Plug, California Standard | | • | | • |
| **CS8365** | | 50 | 3Ø,250 | Plug, California Standard | | • | | • |
| **CS8165** | | 50 | 3Ø,480 | Plug, California Standard | | • | | • |
| **3765** | | 50 | 250VDC. 600VAC | Plug, Corrosion-Resistant | | • | | • |
| **7765**** | | 50 | 250VDC. 600VAC | Plug, Corrosion-Resistant | | • | | • |

*AC Only
**Devices for replacement use only in existing installations.

**See NEMA Configuration chart on inside back cover.**

Ready to wire, ready to perform

# READY TO BOOST PRODUCTIVITY.

## Extra-Hard Use Specification Grade Plugs & Connectors

- Get superior durability in commercial and industrial use — a great choice for tools, extension cords, machines, and lighting
- Nylon housing for superior impact and chemical resistance

**Industrial-strength, brass alloy plug blades and connector contacts** resist heat rise and provide excellent conductivity.

**Quick-thread assembly screws and cord-grip screws** come backed out and ready to wire.

**Single Plane Wiring engineered for speed —** backed out and ready to wire.

**Color-coded terminal screws** positioned on the same plane and backed out for fast, reliable installation.

**See-through, thermoplastic terminal chamber** for clear views of terminals and wire connections.

**Double-wipe, firm-grip ground contact and triple-wipe power contacts** guarantee superior connections.

**Rugged, external, two-piece cord grip** with offset jaws provides uniform pressure for superior conductor retention.

**Recessed cord-grip screw** reduces screwdriver slippage and enhances safety.

**PS5269X**

**PS5266X**



## Extra-Hard Use Ground Continuity Monitoring (GCM) Plugs & Connectors

- Superior durability in commercial and industrial use
- Integral, continuous ground continuity and power-status indication enhances safety

**PS5266XGCM, PS5269XGCM**

## Rubber Watertight Plugs & Connectors

- Rugged performers for commercial or industrial wet indoor or outdoor use with shop tools, machines and extension cords
- Rubber dust-tight and watertight body provides chemical resistance

**14W47**

## Clamp-Lock™ Plugs & Connectors

- Installs 3x faster than conventional connections
- Color-coded levers enable terminal identification and reduce the chance of wiring errors
- Speedy, patented cam-lever termination provides solid, dependable connections

**PS515PCLB, PS515CCLB**

## Rubber Dust-Tight Plugs & Connectors

- Rugged choices for commercial or industrial dry outdoor use with shop tools and extension cords
- Rubber dust-tight body provides chemical resistance
- Clamping cord grip provides excellent conductor retention

**1447**

## Medium-Duty Plugs & Connectors

- Reliable choices for residential and light commercial tool and extension cord use
- Open terminal provides visual confirmation of correct termination

**4867Y, 5276BK**

## MaxGrip M³ Plugs & Connectors

- Tough, nylon construction delivers crush and impact resistance that exceeds hospital grade and Fed Spec requirements
- Self-hinge body swings wide open to enable fast, tight, clean connections

**PS5969Y, PS5965Y**

# Straight Blade Plugs & Connectors

PS5266X

PS5269X

PS5266SSAN

PS5266XHG

PS5269XHG

PS5266XGCM

PS5269XGCM

5276BK

**IP20**
Suitability

| Catalog Number | Rating A. | Rating V. | Description | NEMA Config. No. |
|---|---|---|---|---|
| **Extra-Hard Use (EHU) – Specification Grade**†‡ (Cord Diameter .230" – .720") | | | | |
| **PS5266X*** | 15 | 125 | Plug, Black & Gray | 5-15P |
| **CR5266X** | 15 | 125 | Plug, Corrosion-Resistant, Yellow & White | 5-15P |
| **PS5269X*** | 15 | 125 | Connector, Black & Gray | 5-15R |
| **CR5269X** | 15 | 125 | Connector, Corrosion-Resistant, Yellow & White | 5-15R |
| **PS5366X** | 20 | 125 | Plug, Black & White | 5-20P |
| **PS5369X** | 20 | 125 | Connector, Black & White | 5-20R |
| **PS5666X** | 15 | 250 | Plug, Black & White | 6-15P |
| **PS5669X** | 15 | 250 | Connector, Black & White | 6-15R |
| **PS5466X** | 20 | 250 | Plug, Black & White | 6-20P |
| **PS5469X** | 20 | 250 | Connector, Black & White | 6-20R |
| **PS5766X** | 15 | 277 | Plug, Black & White | 7-15P |
| **PS5866X** | 20 | 277 | Plug, Black & White, Cord Diameter .385" – 1.150" | 7-20P |
| **Extra-Hard Use (EHU) – Specification Grade Angle Plugs**†‡ (Cord Diameter .320" – .655") | | | | |
| **PS5266SSAN** | 15 | 125 | Plug, Black & White | 5-15P |
| **PS5366SSAN** | 20 | 125 | Plug, Black & White | 5-20P |
| **PS5666SSAN** | 15 | 250 | Plug, Black & White | 6-15P |
| **PS5466SSAN** | 20 | 250 | Plug, Black & White | 6-20P |
| *Available in Gray (add GRY to part #) or Black (add BK to part #) interior. | | | | |
| **Extra-Hard Use (EHU) – Hospital Grade**†‡ (Cord Diameter .230" – .720") | | | | |
| **PS5266XHG** | 15 | 125 | Plug, Black & Clear | 5-15P |
| **PS5269XHG** | 15 | 125 | Connector, Black & Clear | 5-15R |
| **PS5366XHG** | 20 | 125 | Plug, Black & Clear | 5-20P |
| **PS5369XHG** | 20 | 125 | Connector, Black & Clear | 5-20R |
| **PS5666XHG** | 15 | 250 | Plug, Black & Clear | 6-15P |
| **PS5669XHG** | 15 | 250 | Connector, Black & Clear | 6-15R |
| **PS5466XHG** | 20 | 250 | Plug, Black & Clear | 6-20P |
| **PS5469XHG** | 20 | 250 | Connector, Black & Clear | 6-20R |
| **Extra-Hard Use (EHU) – Hospital Grade Angle Plugs**†‡ (Cord Diameter .320" – .655") | | | | |
| **PS5266HGAN** | 15 | 125 | Plug, Black & Clear | 5-15P |
| **PS5366HGAN** | 20 | 125 | Plug, Black & Clear | 5-20P |
| **PS5666HGAN** | 15 | 250 | Plug, Black & Clear | 6-15P |
| **PS5466HGAN** | 20 | 250 | Plug, Black & Clear | 6-20P |
| **Extra-Hard Use (EHU) – Ground Continuity Monitoring (GCM)**†‡ (Cord Diameter .230" – .720") | | | | |
| **PS5266XGCM** | 15 | 125 | Plug, Black & Clear | 5-15P |
| **PS5269XGCM** | 15 | 125 | Connector, Black & Clear | 5-15R |
| **PS5366XGCM** | 20 | 125 | Plug, Black & Clear | 5-20P |
| **PS5369XGCM** | 20 | 125 | Connector, Black & Clear | 5-20R |
| **PS5666XGCM** | 15 | 250 | Plug, Black & Clear | 6-15P |
| **PS5669XGCM** | 15 | 250 | Connector, Black & Clear | 6-15R |
| **PS5466XGCM** | 20 | 250 | Plug, Black & Clear | 6-20P |
| **PS5469XGCM** | 20 | 250 | Connector, Black & Clear | 6-20R |
| **Dead Front** (Cord Diameter .230" – .655") | | | | |
| **5276BK** | 15 | 125 | Plug, Black | 5-15P |
| **5269BK** | 15 | 125 | Connector, Black | 5-15R |
| **5765BK** | 20 | 125 | Plug, Black | 5-20P |
| **5374BK** | 20 | 125 | Connector, Black | 5-20R |
| **5666BK** | 15 | 250 | Plug, Black | 6-15P |
| **5669BK** | 15 | 250 | Connector, Black | 6-15R |
| **5864BK** | 20 | 250 | Plug, Black | 6-20P |
| **5866BK** | 20 | 250 | Connector, Black | 6-20R |

† c UL us Compliant

‡ FSUL WC596 Compliant

# Straight Blade Plugs & Connectors

4867Y

PS5965Y

PS5965O

PS5969Y

PS5969O

1447

14W47

| Catalog Number | Rating A. | Rating V. | Description | NEMA Config. No. |
|---|---|---|---|---|
| **Medium Duty**† (Cord Diameter .250" – .600") | | | | |
| **4867Y** | 15 | 125 | Plug, Yellow | 5-15P |
| **4887Y** | 15 | 125 | Connector, Yellow | 5-15R |
| **Hospital Grade MaxGrip® M³**†‡ (Cord Diameter .230" – .720") | | | | |
| **PS8115GRY** | 15 | 125 | Hospital Grade Plug, Gray | 5-15P |
| **PS8119GRY** | 15 | 125 | Hospital Grade Connector, Gray | 5-15R |
| **MaxGrip M³**† (Cord Diameter .230" – .720") | | | | |
| **PS5965Y** | 15 | 125 | Plug, Yellow | 5-15P |
| **PS5965GRY** | 20 | 125 | Plug, Gray | 5-20P |
| **PS5965O** | 15 | 125 | Plug, Orange | 5-15P |
| **PS5965BK** | 15 | 125 | Plug, Black | 5-15P |
| **PS5969Y** | 15 | 125 | Connector, Yellow | 5-15R |
| **PS5969GRY** | 15 | 125 | Connector, Gray | 5-15R |
| **PS5969O** | 15 | 125 | Connector, Orange | 5-15R |
| **PS5969BK** | 15 | 125 | Connector, Black | 5-15R |
| **PS5364Y**‡ | 20 | 125 | Plug, Yellow | 5-20P |
| **PS5364GRY**‡ | 20 | 125 | Plug, Gray | 5-20P |
| **PS5369Y**‡ | 20 | 125 | Connector, Yellow | 5-20R |
| **PS5369GRY**‡ | 20 | 125 | Connector, Gray | 5-20R |
| **PS5666Y**‡ | 15 | 250 | Plug, Yellow | 6-15P |
| **PS5669Y**‡ | 15 | 250 | Connector, Yellow | 6-15R |
| **PS5464Y**‡ | 20 | 250 | Plug, Yellow | 6-20P |
| **PS5469Y**‡ | 20 | 250 | Connector, Yellow | 6-20R |
| **Rubber Dust-Tight** (Cord Diameter .335" – .640") | | | | |
| **1447** | 15 | 125 | Plug, Rubber Yellow | 5-15P |
| **1547** | 15 | 125 | Connector, Rubber Yellow | 5-15R |
| **1433P** | 20 | 125 | Plug, Rubber Yellow | 5-20P |
| **1533** | 20 | 125 | Connector, Rubber Yellow | 5-20R |
| **1449** | 15 | 250 | Plug, Rubber Yellow | 6-15P |
| **1549** | 15 | 250 | Connector, Rubber Yellow | 6-15R |
| **1448** | 20 | 250 | Plug, Rubber Yellow | 6-20P |
| **1548** | 20 | 250 | Connector, Rubber Yellow | 6-20R |
| **Watertight** (Cord Diameter .062" – .625") | | | | |
| **14W47** | 15 | 125 | Plug, Rubber Yellow | 5-15P |
| **15W57** | 15 | 125 | Connector, Rubber Yellow | 5-15R |
| **14W33** | 20 | 125 | Plug, Rubber Yellow | 5-20P |
| **15W33** | 20 | 125 | Connector, Rubber Yellow | 5-20R |
| **14W49** | 15 | 250 | Plug, Rubber Yellow | 6-15P |
| **15W49** | 15 | 250 | Connector, Rubber Yellow | 6-15R |
| **14W48** | 20 | 250 | Plug, Rubber Yellow | 6-20P |
| **15W58** | 20 | 250 | Connector, Rubber Yellow | 6-20R |
| **Turnlok® Watertight Plugs & Connectors** | | | | |
| **PS26W47** | 20 | 125 | Turnlok Plug, Rubber Yellow | L5-20P |
| **PS27W47** | 20 | 125 | Turnlok Connector, Rubber Yellow | L5-20R |
| **PS28W47** | 30 | 125 | Turnlok Plug, Rubber Yellow | L5-30P |
| **PS29W47** | 30 | 125 | Turnlok Connector, Rubber Yellow | L5-30R |

**IP20** Suitability

**IP67** Suitability

**IP67** Suitability



**NEMA 5-15R** **NEMA 5-15P** **NEMA 6-15R** **NEMA 6-15P** **NEMA 5-20R** **NEMA 5-20P** **NEMA 6-20R** **NEMA 6-20P** **NEMA 7-15P** **NEMA 7-20P**

†c UL us Compliant

‡FSUL WC596 Compliant

**All devices listed on this page conform to NEMA WD-1 and WD-6**

Pass & Seymour Pin and Sleeve devices designed to

# PERFORM UNDER SERIOUS PRESSURE.

**Arrives ready to wire, with cord grip open** and cable-ready; terminal screws come backed out and ready to wire.

**Cover with integral neoprene gasket** provides watertight seal.

**Revolutionary, hinged cord grip** for durable performance and ease of installation.

**Nickel-plated brass pins** provide extra corrosion resistance without sacrificing electrical conductivity.

**Locking ring with an integral neoprene gasket** provides watertight seal when plug and connector/receptacle are mated.

**Natural-rubber grommets** provide watertight protection at cable entry.

## Safety Switches & IEC 309 Industrial Products

- Maximum durability for minimum downtime
- Quick, no-guesswork wiring
- Guaranteed interchangeability with IEC products

# North American Watertight Devices

| IP67 Suitability | | | | | |
|---|---|---|---|---|---|
| | Configuration | | | | |
| Poles & Wires | Recep./ Conn. | Plug/ Inlet | Voltage/ Color Coding | Plug | Connector |
| **20 Amps** | | | | | |
| 2P3W | | | 125 | PS320P4W | PS320C4W |
| 2P3W | | | 250 | PS320P6W | PS320C6W |
| 2P3W | | | 277 | PS320P5W | PS320C5W |
| 3P4W | | | 125/250 | PS420P12W | PS420C12W |
| 3P4W | | | 3ø 250 | PS420P9W | PS420C9W |
| 3P4W | | | 3ø 480 | PS420P7W | PS420C7W |
| 3P4W | | | 3ø 600 | PS420P5W | PS420C5W |
| 4P5W | | | 3øY 120/208 | PS520P9W | PS520C9W |
| 4P5W | | | 3øY 277/480 | PS520P7W | PS520C7W |
| 4P5W | | | **3øY 347/600** | PS520P5W | PS520C5W |
| **30 Amps** | | | | | |
| 2P3W | | | 125 | PS330P4W | PS330C4W |
| 2P3W | | | 250 | PS330P6W | PS330C6W |
| 3P4W | | | 125/250 | PS430P12W | PS430C12W |
| 3P4W | | | 3ø 250 | PS430P9W | PS430C9W |
| 3P4W | | | 3ø 480 | PS430P7W | PS430C7W |
| 3P4W | | | 3ø 600 | PS430P5W | PS430C5W |
| 3P4W* | | | 380/440 | PS430P3W | PS430C3W |
| 4P5W | | | 3øY 120/208 | PS530P9W | PS530C9W |
| 4P5W | | | 3øY 277/480 | PS530P7W | PS530C7W |
| 4P5W | | | 3øY 347/600 | PS530P5W | PS530C5W |

| IP67 Suitability | | | | | |
|---|---|---|---|---|---|
| | Configuration | | | | |
| Poles & Wires | Recep./ Conn. | Plug/ Inlet | Voltage/ Color Coding | Plug | Connector |
| **60 Amps** | | | | | |
| 2P3W | | | 125 | PS360P4W | P0S360C4W |
| 2P3W | | | 250 | PS360P6W | PS360C6W |
| 2P3W | | | 480 | PS360P7W | PS360C7W |
| 3P4W | | | 125/250 | PS460P12W | PS460C12W |
| 3P4W | | | 3ø 250 | PS460P9W | PS460C9W |
| 3P4W | | | 3ø 480 | PS460P7W | PS460C7W |
| 3P4W | | | 3ø 600 | PS460P5W | PS460C5W |
| 4P5W | | | 3øY 120/208 | PS560P9W | PS560C9W |
| 4P5W | | | 3øY 277/480 | PS560P7W | PS560C7W |
| 4P5W | | | 3øY 347/600 | PS560P5W | PS560C5W |
| **100 Amps** | | | | | |
| 2P3W | | | 250 | PS3100P6W | PS3100C6W |
| 2P3W | | | 480 | PS3100P7W | PS3100C7W |
| 3P4W | | | 125/250 | PS4100P12W | PS4100C12W |
| 3P4W | | | 3ø 250 | PS4100P9W | PS4100C9W |
| 3P4W | | | 3ø 480 | PS4100P7W | PS4100C7W |
| 3P4W | | | 3ø 600 | PS4100P5W | PS4100C5W |
| 4P5W | | | 3øY 120/208 | PS5100P9W | PS5100C9W |
| 4P5W | | | 3øY 277/480 | PS5100P7W | PS5100C7W |
| 4P5W | | | 3øY 347/600 | PS5100P5W | PS5100C5W |

***Application Specific — Refrigerant Containers**

## North American Splashproof Devices

| IP44 Suitability | | | |  |  |
|---|---|---|---|---|---|
| | Configuration | | | | |
| Poles & Wires | Recep./ Conn. | Plug/ Inlet | Voltage/ Color Coding | Plug | Connector |
| **20 Amps** | | | | | |
| 2P3W | | | 125 | PS320P4S | PS320C4S |
| 2P3W | | | 250 | PS320P6S | PS320C6S |
| 3P4W | | | 3ø 250 | PS420P9S | PS420C9S |
| 3P4W | | | 3ø 480 | PS420P7S | PS420C7S |
| **30 Amps** | | | | | |
| 2P3W | | | 125 | PS330P4S | PS330C4S |
| 2P3W | | | 250 | PS330P6S | PS330C6S |
| 3P4W | | | 3ø 250 | PS430P9S | PS430C9S |
| 3P4W | | | 3ø 480 | PS430P7S | PS430C7S |
| 3P4W | | | 3ø 600 | PS430P5S | PS430C5S |
| 4P5W | | | 3øY 120/208 | PS530P9S | PS530C9S |
| 4P5W | | | 3øY 347/600 | PS530P5S | PS530C5S |
| **60 Amps** | | | | | |
| 2P3W | | | 250 | PS360P6S | PS360C6S |
| 2P3W | | | 480 | PS360P7S | PS360C7S |
| 3P4W | | | 125/250 | PS460P12S | PS460C12S |
| 3P4W | | | 3ø 250 | PS460P9S | PS460C9S |
| 3P4W | | | 3ø 480 | PS460P7S | PS460C7S |
| 3P4W | | | 3ø 600 | PS460P5S | PS460C5S |
| 4P5W | | | 3øY 120/208 | PS560P9S | PS560C9S |
| 4P5W | | | 3øY 277/480 | PS560P7S | PS560C7S |

## International Splashproof Devices

| | | | | Splashproof (IP44 Suitability) | |
|---|---|---|---|---|---|
| | | | |  |  |
| | Configuration | | | | |
| Poles & Wires | Recep./ Conn. | Plug/ Inlet | Voltage/ Color Coding | Plug | Connector |
| **16 Amps** | | | | | |
| 2P3W | | | 110/120 | 51940 | 51980 |
| 2P3W | | | 220/240 | 52042 | 52082 |
| 2P3W | | | 380/415 | 52242 | 52282 |
| 3P4W | | | 220/240 | 52043 | 52083 |
| 3P4W | | | 380/415 | 52243 | 52283 |
| 4P5W | | | 220/240 | 52044 | 52084 |
| 4P5W | | | 220/380 240/415 | 52244 | 52284 |
| **32 Amps** | | | | | |
| 2P3W | | | 220/240 | 52742 | 52782 |
| 2P3W | | | 380/415 | 52942 | 52982 |
| 3P4W | | | 220/240 | 52743 | 52783 |
| 3P4W | | | 380/415 | 52943 | 52983 |
| 4P5W | | | 220/240 | 52744 | 52784 |
| 4P5W | | | 220/380 240/415 | 52944 | 52984 |
| **63 Amps** | | | | | |
| 2P3W | | | 110/120 | 53582 | |
| 2P3W | | | 220/240 | 53642 | 53682 |
| 3P4W | | | 220/240 | 53643 | 53683 |
| 3P4W | | | 380/415 | 53843 | 53883 |
| 4P5W | | | 220/240 | 53644 | 53684 |
| 4P5W | | | 220/380 240/415 | 53844 | 53884 |

# NEMA Configurations
# Locking Plugs & Receptacles

| | 15 AMPERE | | 20 AMPERE | | 30 AMPERE | |
|---|---|---|---|---|---|---|
| | RECEPTACLE | PLUG | RECEPTACLE | PLUG | RECEPTACLE | PLUG |
| **2 Pole, 2 Wire Non-Grounding** | | | | | | |
| L1 125V | L1-15R | L1-15P | | | | |
| L2 250V | | | L2-20R | L2-20P | | |
| **2 Pole, 3 Wire Grounding** | | | | | | |
| L5 125V | L5-15R | L5-15P | L5-20R | L5-20P | L5-30R | L5-30P |
| L6 250V | L6-15R | L6-15P | L6-20R | L6-20P | L6-30R | L6-30P |
| L7 277VAC | L7-15R | L7-15P | L7-20R | L7-20P | L7-30R | L7-30P |
| L24 347VAC | | | L24-20R | L24-20P | | |
| L8 480VAC | | | L8-20R | L8-20P | L8-30R | L8-30P |
| L9 600VAC | | | L9-20R | L9-20P | L9-30R | L9-30P |
| **3 Pole, 3 Wire Non-Grounding** | | | | | | |
| L10 125/250V | | | L10-20R | L10-20P | L10-30R | L10-30P |
| L11 3ø250V | | | L11-20R | L11-20P | L11-30R | L11-30P |
| L12 3ø480V | | | L12-20R | L12-20P | L12-30R | L12-30P |
| L13 3ø600V | | | | | L13-30R | L13-30P |
| **3 Pole, 4 Wire Grounding** | | | | | | |
| L14 125/250V | | | L14-20R | L14-20P | L14-30R | L14-30P |
| L15 3ø250V | | | L15-20R | L15-20P | L15-30R | L15-30P |
| L16 3ø480V | | | L16-20R | L16-20P | L16-30R | L16-30P |
| L17 3ø600V | | | | | L17-30R | L17-30P |
| **4 Pole, 4 Wire Non-Grounding** | | | | | | |
| L18 3øY 120/208V | | | L18-20R | L18-20P | L18-30R | L18-30P |
| L19 3øY 277/480V | | | L19-20R | L19-20P | L19-30R | L19-30P |
| L20 3øY 347/600V | | | L20-20R | L20-20P | L20-30R | L20-30P |
| **4 Pole, 5 Wire Grounding** | | | | | | |
| L21 3øY 120/208V | | | L21-20R | L21-20P | L21-30R | L21-30P |
| L22 3øY 277/480V | | | L22-20R | L22-20P | L22-30R | L22-30P |
| L23 3øY 347/600V | | | L23-20R | L23-20P | L23-30R | L23-30P |

| LABEL DESIGNATION | |
|---|---|
| **X, Y, Z** | Hot Lead |
| **W** | Neutral Lead |
| **G** | Grounding Lead |

**Open Slots**
Indicate receptacle configurations (female).




**Closed Slots**
Indicate plug blade configurations (male).

**PS40MBBK, PS40FBBK**

## Cam-Type Devices

- Uncompromising quality and performance
- Interchangeable with other manufacturers' cam-type devices
- Weatherproof connection
- Ideal for a wide range of applications with a need for reliable portable/ temporary power

designed to be better.™

**For additional technical or application-specific information, call 800-223-4185 or visit our website at www.legrand.us/PassandSeymour. We're eager to put our expertise to work for you.**

**Electrical Wiring Systems**

P.O. Box 4822
Syracuse, NY 13221-4822
800.776.4035
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US