WATTSTOPPER®

DIMMERS

Smarter spaces, lower costs, more control

designed to be better.™

legrand®

Legrand provides the most expansive offering of lighting controls for managing delivery of light and data. Wattstopper's unmatched portfolio of lighting controls enables sustainability and increases energy efficiency.

What makes Wattstopper's dimmers so special? They simply work. We have a solution for every lamp, every load, in every setting imaginable.

From saving energy to setting the mood, our extensive line of easy-to-use dimming solutions delivers an unmatched level of control wherever you live, work, and play. Visually appealing and easy to install, they are a great way to enhance a room's ambiance while reducing power consumption.

Dimmers to handle virtually every type of lamp and load.

CFL/LED DIMMERS
The smart choice for these popular lamps

MULTI-LOCATION DIMMERS
More dimming control meets more style

LED SYSTEMS
Stylish solutions for the latest lighting technologies

INCANDESCENT DIMMERS
A stylish solution for standard lamps

FAN SPEED CONTROLS
A cool way to control airflow in any room

Color Designations*

W	White
LA	Light Almond
I	Ivory
BK	Black
–	Brown
GRY	Gray
NI	Nickel
AB	Antique Brass
DB	Dark Bronze

THE UNIVERSAL DIMMER THAT SIMPLY WORKS

Our new radiant dimmers are all about style. But thanks to our innovative Tru-Universal technology, they radiate simplicity as well. In fact, the radiant Tru-Universal Dimmer is the only dimmer that works with virtually every lamp and load. It's not just the technology that makes radiant the perfect choice, but also its user-friendly features:

- Wider slide controller for easier dimming operation
- Ergonomic slider grip for more intuitive finger control
- Larger paddle switch that is easy to see and use
- Sleek, modern design that matches today's style
- A locator LED glows when OFF to make the dimmer easier to find in the dark



POTENTIALLY **REPLACES** > **30** **SKUs**

Since only one dimmer is needed for virtually every lamp and load, it reduces the number of SKUs needed for stocking or hauling around.

With interchangeable faces in popular colors like White, Ivory, and Light Almond, there is no longer a need to stock all colors — they are easily changed on-site.

FAST, COST-EFFECTIVE INSTALLATION

Ganging commercial dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change everything. Unlike the others, Titan Dimmers provide a complete solution that saves time and money and offers end-users a superior, more convenient, and better-looking multi-gang installation.

Included end-caps and spacers screw directly to heat sinks; center plate easily snaps on and off

Improved heat management enables superior load ratings

Enclosed slider helps prevent dust and dirt contamination

Exclusive adjustable limit control in incandescent dimmers saves energy, extends bulb life, and reduces maximum output by up to 10 percent

Power-failure memory retains presets through power outages

CD703PW

radiant® Dimmers

PART NO.*	DESCRIPTION	COLOR	RATING
RH703PTUTC	**Tru-Universal™** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 450W CFL/LED; 700W Incandescent, Halogen & ELV; 500VA MLV; 5.5A EFL
RH703PTUW		White	
RHCL453PTC	**CFL/LED** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 450W CFL/LED; 700W Incandescent
RHCL453PW		White	
RHFB83PTC	**Fluorescent** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 8A
RHFB83PW		White	
RH4FBL3PTC	**LED/Fluorescent** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	0–10V
RH4FBL3PW		White	
RHLV703PTC	**Magnetic Low Voltage** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 700VA
RHLV703PW		White	
RHLV1103PTC	**Magnetic Low Voltage** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1100VA
RHLV1103PW		White	
RH703PTC	**Incandescent** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 700W
RH1103PTC		Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1100W
RH1103PW		White	
RHDH163PTC	**Fan Speed Control** De-hummer, Single Pole/3-Way Uses RHKIT Covers	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1.6A
RHDH163PW		White	
HCL453PMMTC	**CFL/LED Multi-location Master Dimmer** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 450W CFL/LED; 700W Incandescent
HCL453PMMW		White	
HDH163PMMTC	**Fan Speed Control Multi-location Master** De-hummer, Single Pole/3-Way	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1.6A
HDH163PMMW		White	
HMRTC	**Multi-location Remote** Single Pole/3-Way	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V
HMRW		White	

PART NO.*	DESCRIPTION	COLOR
RHKIT	Interchangeable Face Plate	Ivory, White, Light Almond, Black, Brown, Gray, Nickel, Antique Brass, Dark Bronze
HMKIT	Multi-location Dimmer, Interchangeable Face Plate	
HDHKIT	Multi-location De-hummer, Fan Speed Control, Interchangeable Face Plate	
HMRKIT	Multi-location Remote Dimmer, Interchangeable Face Plate	

*See color designations on page 2

All devices are c UL us LISTED

TRU-UNIVERSAL DIMMERS

- Work with virtually every lamp and load
- Self-calibrate to match lamp type
- Allow you to dial in the performance of the lamp you choose

TITAN® SERIES DIMMERS

- Capacity to handle large loads
- Included screwless wall plate components make it easy to assemble multi-gang configurations, saving money and time
- Optional built-in label holder enables instant circuit identification; looks clean and professional
- Power-failure memory retains presets through power outages

Titan® Series Dimmers

PART NO.*	DESCRIPTION	COLOR	RATING
CD1103P	**Incandescent**	White, Ivory, Gray, Black, Light Almond, Brown	40-1100W
CD2003P	**Incandescent**		40-2000W
CDLV703P	**Magnetic Low Voltage**		40-700VA
CDLV1103P	**Magnetic Low Voltage**		40-1600VA
CDFB83P	**Two-Wire Fluorescent**		0.33-8A
CDFB163P	**Two-Wire Fluorescent**		0.33-16A
CDFB103P277	**Two-Wire Fluorescent**		0.33-16A
CD3FB163P	**Three-Wire Fluorescent**		0.33-16A
CD3FB103P277	**Three-Wire Fluorescent**		0.33-10A
CD4FB	**Four-Wire 0-10V, Fluorescent**		Up to 60 ballasts
CD4FBL	**Four-Wire 0-10V, Fluorescent**		30mA
CD4FBL3P	**Four-Wire 0-10V, Fluorescent**		30mA
CDSC6	**Fan Speed Control**		0.33-6A

*See color designations on page 2

All devices are c UL us LISTED

STYLISHLY SIMPLE DIMMING SOLUTIONS

Multi-location Touch Dimmers

PART NO.*	DESCRIPTION	COLOR	RATING
TDA603	**Master Dimmer w/ Neutral** Single Pole/3-Way	White, Ivory, Almond, Light Almond, Gray, Black	120V; 25-600W
TD603	**Incandescent Master Dimmer** Single Pole/3-Way		120V; 40-600W
TDFC1A	**Fan Speed Control Master** Single Pole/3-Way		120V; 1.5A
TDR	**Remote**		120V

*See color designations on page 2

All devices are c UL us LISTED

MULTI-LOCATION TOUCH DIMMERS

- Easily dim from multiple locations
- Change 3-Way and 4-Way switches to dimming
- Fan Speed Control also available

FOR EVERY SETTING

TOGGLE PRESET DIMMERS

- Convenient preset dimming control
- Combines ON/OFF toggle with separate dimming wheel for light-level control
- Matches appearance of standard toggle switches

Toggle Dimmers

PART NO.*	DESCRIPTION	COLOR	RATING
T1000	**Incandescent** Single Pole, Non-Preset	Brown, Ivory, Light Almond, White	120V; 1000W
T1003	**Incandescent** 3-Way, Non-Preset		
T600	**Incandescent** Single Pole, Non-Preset	Brown, Ivory, Light Almond, White	120V; 600W
TLV603	**Magnetic Low Voltage** 3-Way, Non-Preset	Ivory, Light Almond, White	120V; 600VA
TD1103P	**Incandescent** Single Pole/3-Way, Preset	Black, Brown, Ivory, Light Almond, White	120V; 1100W
TD703P			120V; 700W
TDFB83P	**Fluorescent** Single Pole/3-Way, Two Wire, Preset	Black, Brown, Ivory, Light Almond, White	120V; 8A
TSC5	**Fan Speed Control** Adjustable Trim, Non-Preset	Ivory, Light Almond, White	120V; 5A
TDDH163P	**Fan Speed Control** De-hummer	Black, Brown, Ivory, Light Almond, White	120V; 1.6A
TDCL453P	**CFL/LED** Single Pole/3-Way, Preset	Black, Brown, Ivory, Light Almond, White	120V; 450W CFL/LED; 700W Incandescent

*See color designations on page 2

All devices are c UL US LISTED

Wide Slide Dimmers

PART NO.*	DESCRIPTION	COLOR	RATING
WS1000TC	**Incandescent** Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1000W
WS1100TC	**Incandescent** Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1100W
WS1103PTC	**Incandescent** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	
WS700TC	**Incandescent** Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 700W
WS703PTC	**Incandescent** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	
WS703PW		White	
WSCL450TC	**CFL/LED/Incandescent** Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120VAC; 450W
WSCL450W		White	
WSCL453PTC	**CFL/LED/Incandescent** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	
WSCL453PW		White	
WS4FBL3PTC	**LED/Fluorescent** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	0–10V
WS4FBL3PW		White	
WSSC53PW	**Fan Speed Control** Variable Speed, Preset	White	120V; 5A
WSDH16TC	**Fan Speed Control** De-hummer, Single Pole	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1.6A
WSDH16W		White	
WSLV700TC	**Magnetic Low Voltage** Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 700VA
WSLV703PTC	**Magnetic Low Voltage** Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	

PART NO.*	DESCRIPTION	COLOR
WSKIT	Interchangeable Face Plate, Non-Preset	Black, Brown, Ivory, Light Almond, White
WSKITP	Interchangeable Face Plate, Preset	

*See color designations on page 2

All devices are c UL us LISTED

WIDE SLIDE DIMMERS

- Available in preset and slide-to-OFF models
- 3 interchangeable face plates in one package
- Faces snap easily into place and match any décor
- Operational in single-pole and 3-Way applications

SCREWLESS WALL PLATES

- Premium finishes that stand up to constant use
- Hidden screws create a sleek, seamless accent
- Available in single- and multiple-gang configurations

LS SERIES DIMMERS

- Ergonomic design and solid, quality material
- Sleek, sculpted, contemporary design
- Patented Snap-In Light Module for easy nighttime visibility (sold separately)

LS Series Dimmers

PART NO.*	DESCRIPTION	COLOR	RATING
LS1000	**Incandescent** Single Pole, Non-Preset	Black, Brown, Ivory, Light Almond, White	120V; 1000W
LS1000P	**Incandescent** Single Pole, Preset		
LS1003P	**Incandescent** 3-Way, Preset		
LS600	**Incandescent** Single Pole, Non-Preset	Black, Brown, Ivory, Light Almond, White	120V; 600W
LS600LWV	**Incandescent** Lighted, Single Pole, Non-Preset	White	
LS600P	**Incandescent** Single Pole, Preset	Black, Brown, Ivory, Light Almond, White	
LS603P	**Incandescent** 3-Way, Preset		
LS603PLWV	**Incandescent** Lighted, 3-Way, Preset	White	
LSCL450	**CFL/LED/Incandescent** Single Pole, Non-Preset	Black, Brown, Ivory, Light Almond, White	120VAC; 450W CFL/LED; 700W Incandescent
LSCL453P	**CFL/LED/Incandescent** 3-Way, Preset		
LSCLDC163P	**CFL/LED/Incandescent** Single Pole/3-Way, Preset Dimmer with Single Pole/3-Way, 3-Speed De-hummer Fan Control	Black, Brown, Ivory, Light Almond, White	1.6A (Fan Control); 120VAC, 150W CFL/LED; 300W Incandescent (Dimmer)
LSLV600	**Magnetic Low Voltage** Single Pole, Non-Preset	Black, Brown, Ivory, Light Almond, White	120V; 600VA
LSLV600P	**Magnetic Low Voltage** Single Pole, Preset		
LSLV603P	**Magnetic Low Voltage** 3-Way, Preset		
LSDC16V	**Fan Speed Control** 3-Speed De-hummer Fan Speed Control, Non-Preset with Single Pole Incandescent Dimmer	Brown, Ivory, Light Almond, White	1.6A (Fan Control); 120V; 300W Incandescent (Dimmer)
LSDC16PV	**Fan Speed Control** 3-Speed De-hummer Fan Speed Control, Preset with Single Pole Incandescent Dimmer	Brown, Black	
LSDH16V	**Fan Speed Control** 4-Speed De-hummer, Non-Preset	Black, Brown, Ivory, Light Almond, White	1.6A
LSSC5	**Fan Speed Control** Single Pole with Adjustable Trim, Non-Preset		5A
LSSC5P	**Fan Speed Control** Single Pole with Adjustable Trim, Preset		

*See color designations on page 2

All devices are c UL us LISTED

Rotary Series Dimmers

PART NO.*	DESCRIPTION	COLOR	RATING
R1000V	**Incandescent** Single Pole with RFI Filtering, Non-Preset	Ivory, Light Almond, White	120V; 1000W
R1000PV	**Incandescent** Single Pole with RFI Filtering, Preset		
R1003PV	**Incandescent** 3-Way with RFI Filtering, Preset		
R600V	**Incandescent** Single Pole with RFI Filtering, Non-Preset	Ivory, Light Almond, White	120V; 600W
R600PV	**Incandescent** Single Pole with RFI Filtering, Preset		
R600PLTKV	**Incandescent** Single Pole with RFI Filtering, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	
R603PV	**Incandescent** 3-Way with RFI Filtering, Preset	Ivory, Light Almond, White	
R603PLTKV		Three Interchangeable Face Colors: Ivory, White, Light Almond	

*See color designations on page 2

All devices are c UL us LISTED

ROTARY DIMMERS

- Full-range rotary dimming
- Ground lead included on all models
- All models fit standard toggle wall plate

DR Series Dimmers

PART NO.*	DESCRIPTION	COLOR	RATING
DRCL453P	**CFL/LED** Single Pole/3-Way, Preset	Black, Brown, Ivory, Light Almond, White	120V; 450W CFL/LED; 700W Incandescent
DR703PV	**Incandescent** Single Pole/3-Way with Pilot Light, Preset	Black, Brown, Ivory, Light Almond, White	120V; 700W
DRLV1103P	**Magnetic Low Voltage** Single Pole/3-Way with Pilot Light, Preset	Black, Brown, Ivory, Light Almond, White	120V; 1100VA
DRLV703P			120V; 700VA
DRDH163PV	**Fan Speed Control** 3-Speed De-hummer Fan Speed Control with Single Pole/3-Way, Backlit Speed Indication, Preset	Black, Brown, Ivory, Light Almond, White	120V; 1.6A
DRSC53PV	**Fan Speed Control** Continuously Variable, Single Pole/3-Way, Preset		120V; 5A

*See color designations on page 2

All devices are c UL us LISTED

DR SERIES DIMMERS

- Contemporary style
- Illuminated knob indicates light level
- Snap-In LED modules make dimmers easy to find at night (sold separately)
- Available for incandescent and low-voltage lighting

Wattstopper®

Customer Care
7 am - 7 pm CST
800.927.9287

Technical Support
7 am - 7 pm CST
800.879.8585

Services & Support
www.legrand.us/support/wattstopper

©2016 Legrand. All Rights Reserved. WS20022 12/2016

designed to be better™

legrand®

Wattstopper, North America
www.legrand.us/wattstopper

FOLLOW US