legrand®

Cablofil

FTBE
BLIND END





Hardware included

- M6x12mm square neck carriage bolt (zinc plated)
- M6 serrated flange hex nut (zinc plated)

FEATURES

- Provides closure at ends
- Rigid steel construction
- Can be punched for conduit attachment

	PACK	HEIGHT		WIDTH		PG	BL
	PCS	INCHES	MM	INCHES	MM	STANDARD	
FTBE 50/50	1	2	50	2	50	341 537	960 144
FTBE 50/100	1	2	50	4	100	341 538	960 145
FTBE 50/200	1	2	50	8	200	341 540	960 146
FTBE 50/300	1	2	50	12	300	341 541	960 147
FTBE 100/100	1	4	100	4	100	341 659	960 159
FTBE 100/200	1	4	100	8	200	341 661	960 160
FTBE 100/300	1	4	100	12	300	341 662	960 161
FTBE 100/500	1	4	100	20	500	341 664	960 162
FTBE 100/600	1	4	100	24	600	340 737	960 163

FINISHES			
SYMBOL		MATERIAL	FINISH & STANDARD
STANDARD	PG	Carbon Steel	**Pre-Galvanized:** Continuous Galvanization Before Fabrication ASTM A 653
	BL	Carbon Steel ASTM A510 Grade 1008	**Black Painted:** Black Powder Coated ASTM D 3451

© 2012 Legrand/Cablofil 02/12

Legrand/Cablofil
8319 State Route 4
Mascoutah, IL 62258 USA
1-800-658-4641
618-566-3230
Fax 618-566-3250
www.legrand.us/cablofil