NOTES:

1. NOMINAL IMPEDANCE: 75 ohms
2. F-CONNECTOR TYPE: ANSI/SCTE COMPLIANT SEALED BRASS
3. POWER REQUIREMENTS: NONE
4. INPUT CONNECTIONS: 1
5. OUTPUT CONNECTIONS: 8
6. OPERATING TEMPERATURE: -40° TO 60°C
7. INSERTION LOSS: 11dB







PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED
IN THIS DRAWING IS THE SOLE
PROPERTY OF On-Q/LEGRAND.
ANY REPRODUCTION IN PART OR
AS A WHOLE WITHOUT THE WRITTEN
PERMISSION OF On-Q/LEGRAND
IS PROHIBITED. DRAWING IS SUBJECT
TO CHANGE WITHOUT NOTICE.

on·Q
legrand
P.O. Box 60907
Middletown, PA 17106-0907
1-800-321-2343

TITLE:
1 X 8 ENHANCED PASSIVE VIDEO SPLITTER/COMBINER

SIZE	DWG NO	FILE NAME	CUST REV
A	VM1002	CD-VM1002	1

REVISED DATE	SCALE	SHEET
11/06/07	NONE	1 OF 1

ACAD