




Pass & Seymour

Hospital Grade Devices Extra Heavy-Duty Receptacles Tamper-Resistant 15 & 20A, 125V

TR62-H, TR63-H

Extremely durable receptacles for pediatric locations.

The heavy-gauge brass straps lock into the 100 percent nylon faces and back bodies — ensuring long-term durability. And a sturdy mechanical shutter system helps prevent children from sticking objects into the receptacle. Installation is quick and easy, thanks to screw-pressure-plate back wiring (side wiring is supported too). There is even a back wire clamp on the ground terminal.



Features & Benefits

Auto-ground eliminates the necessity to terminate grounding conductor to device.

Dual mechanical shutter system to help prevent insertion of foreign objects.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

Exclusive patented feature, circuit label on face of device allows permanent and positive circuit identification.

Extra heavy-duty brass, one-piece mounting strap with integral ground for superior structural integrity and long-term performance.



TR63-HI

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

One-piece, nickel-plated triple-wipe power contacts for reliable plug retention.

Field Uses/Vertical Markets

■ Health Care

■ Education

■ Institutional



Pass & Seymour

Hospital Grade Devices Extra Heavy-Duty Receptacles Tamper-Resistant 15 & 20A, 125V

Ordering Information

Catalog Number	Rating A. V.	Color	NEMA Config. No.
Hospital Grade Duplex Receptacles Back & Side Wire			
TR62-HI	15 125	Ivory	5-15R
TR62-HW	15 125	White	5-15R
TR62-H	15 125	Brown	5-15R
TR62-HGRY	15 125	Gray	5-15R
TR62-HRED	15 125	Red	5-15R
TR62-HLA	15 125	Light Almond	5-15R
TR63-HI	20 125	Ivory	5-20R
TR63-HW	20 125	White	5-20R
TR63-H	20 125	Brown	5-20R
TR63-HGRY	20 125	Gray	5-20R
TR63-HRED	20 125	Red	5-20R
TR63-HLA	20 125	Light Almond	5-20R



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Product Guide or visit our web site.

SF704R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour

Hospital Grade Devices Extra Heavy-Duty Receptacles Tamper-Resistant 15 & 20A, 125V




Pass & Seymour

Technical Specifications

3rd Party Compliance	
UL Listed, File Number E140596, Standard UL498.	
Federal Specification WC596, Hospital Grade.	
CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42.	

Performance	
Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



Dimensions for 15 & 20 Amp

Materials			
Face	Nylon	Terminal Screws	#10 Tri-Drive Brass
Back Body	Nylon		(Neutral = Nickel-Plated Steel)
Line Contacts	688 Nickel-Plated Brass	Ground Screw	#10 Hex Tri-Drive Brass
Mounting Strap	.050 688 Brass	Assembly Drive Screw	Zinc-Plated Steel
Ground Contacts	Strap with Integral Ground	Auto-Ground Clip	Brass
Pressure Plate	.031 260 Nickel-Plated Brass	Mounting Screws	Tri-Drive Steel

Warranty


1 Year

Complementary Devices & Accessories




HOSPITAL GRADE DEVICES

- Receptacles, Tamper-Resistant, Decorator
- GFCIs
- TVSS
- Isolated Ground
- Plugs & Connectors




PLUGTAIL™ DEVICES

- Extra Heavy-Duty Hospital Grade Receptacles
- Heavy-Duty Hospital Grade Receptacles
- Extra Heavy-Duty Receptacles




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Decorator Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca