YOUR COMPLETE LINE OF RUGGED,
EASY-TO-INSTALL SOULTIONS.

legrand®

Pass & Seymour

designed to be better.

RECTANGULAR SINGLE-GANG

- **Rugged, die-cast cover plate** with durable nickel or brass finish.
- **Scrub water compliant without caulking,** supplied with foam gasket and O-ring-equipped plugs.
- **Meet UL514C 2007 rev and NEC314.27c requirements** including scrub water for tile floors.

- **Includes receptacle, multimedia divider, Cat 5e jack, and F-connector.**

FB1SRKS1

- **Large box flange** rests on finished floor — no adjustments needed.

- **Swing-bracket mounting,** great for tile floors — eliminates drilling for mounting screws.

ROUND SINGLE-GANG

- **Rugged, die-cast cover plate** with aluminum or brass finish.
- **Smooth, nearly flush appearance** when installed.
- **P&S 3232 or 885 duplex receptacles** included.
- **Multimedia divider** provided in low-voltage models.

- **Snap-in jack holder accommodates two snap-in multimedia jacks** for easy configuration. Choose from wide variety of P&S multimedia jacks for any application.
- **Hinged covers or threaded plugs.**

PS863PC0MAL

- **Extra-deep design** leaves plenty of wiring room.
- **Built-in ground terminal** makes ground bonding easy when required by code.

Catalog Number	Plate Finish	Description	Devices included
Rectangular Single-Gang — wood sub-floors only			
FBISR_	Brass Nickel	Single Receptacle, Threaded Plug	15A Receptacle
FB1SRKS1_	Brass Nickel	Dual-Voltage, #8 Duplex Opening, Threaded Plugs	15A Receptacle, Cat 5e Jack, F-Connector, and Blanks
FB1DR_	Brass Nickel	#8 Duplex Opening, Threaded Plugs	3232 Receptacle
FB1KS4_	Brass Nickel	Low-Voltage #8 Duplex Opening, Threaded Plugs	Cat 5e Jack, F-Connector, and Blanks
Rectangular Steel Single-Gang — wood sub-floors only			
1542FBA	Brass	Steel Box With Single Threaded Plug	Single Receptacle
Rectangular Two-Gang — wood sub-floors only			
FB2DRKS4_	Brass Nickel	Two #8 Openings, Threaded Plugs	3232 Receptacle, Cat 5e Jack, F-Connector, and Blanks
FB2DR2_	Brass Nickel	Two #8 Openings, Threaded Plugs	Two 3232 Receptacles
FB2KS8_	Brass Nickel	Two Low-Voltage #8 Openings, Threaded Plugs	Cat 5e Jack, F-Connector, and Blanks

NOTES

"**B**" suffix in FB Series catalog number denotes brass cover finish. Substitute "**N**" to denote nickel finish.

PS862 Series covers available in hardwood, tile, and carpet models with brass or aluminum finish.

For complete ordering details, ask your P&S representative or distributor.

c UL us LISTED

Catalog Number	Plate Finish	Description	Devices included
Round — wood sub-floors only			
TM1542-BOX	–	38" Cu. In. Plastic Box for use with TM1542 Covers	–
TM1542-XXX	White, Brown, Gray, Black, Light Almond, Paintable Gray	Non-Metallic Cover for use with TM1542-BOX	885 Decorator Receptacle
TM1542-FM	Brass	Low-Profile (1/4") Cover	885 Decorator Receptacle
Round — wood or concrete sub-floors			
PS862D_	Brass Aluminum	#8 Duplex Opening, Hinged Covers	3232 Receptacle
PS862TGFCI_	Brass Aluminum	#26 Decorator Opening, Hinged Covers	885 Decorator Receptacle
PS862TSP_	Brass Aluminum	#8 Duplex Opening, Screw Plugs	3232 Receptacle
PS862TCK12_	Brass Aluminum	Cover Conversion Kit 1-¼" to ½" Screw Plug	–
PS862DPC0MAL	–	#8 Duplex Opening and Two Low-Voltage Openings, Hinged Covers	3232 Receptacle, Cat 5e Jack, F-Connector
Round Components and Kits			
PS862KIT	_	Concrete Kit	Mud Cap, Gasket, Two ¾" Male PVC Conduit Fittings
PS862	_	Box only, covers available separately	Covers available separately

P&S Floor Boxes — the easiest way to put receptacles and multimedia connections everywhere they're needed.

If you've installed P&S Wall, Ceiling, or Fan boxes, you know just what to expect in the P&S Floor Box Line: everything you're looking for. These affordable, high-value solutions bring you convenient access, rugged construction, and support for both line-voltage and low-voltage connections — which are easy to configure and install, because P&S offers a broad selection of wiring devices and multimedia jacks. P&S Floor Boxes install in wood and concrete floors and provide compatibility with a wide range of floor surfaces, including ceramic tile.

With P&S, you can take advantage of all the right choices in round and rectangular styles to accommodate either single- or two-gang applications. There's even a single-gang dual-voltage model — a P&S exclusive!

Learn about all the P&S Floor Box choices.

Additional P&S Floor Box models, accessories, and finish options are available. For complete details, ask your P&S representative or distributor — or visit www.passandseymour.com.

For additional technical or application-specific information, call 800-223-4185 or visit our website at www.legrand.us/passandseymour. We're eager to put our expertise to work for you.

Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-776-4035
www.legrand.us/passandseymour

©2010, Legrand /Pass & Seymour BR1591 6/07 EMA/DG

Distributed by:

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca