RESIDENTIAL DIMMERS & FAN SPEED CONTROLS

radiant™ Fluorescent Dimmers & Fan Speed Controls

RHFB83PW

RHDH163PW

The radiant™ collection is a step up from the standard with simple, classic options in wiring devices, home automation controls, and screwless wall plates that complement today's homes and hospitality settings.

Features

- Part of the radiant™ collection.
- Convenient operation – combines ON/OFF paddle switch with separate slider for dimming control.
- White LED glows when OFF to make dimmer easy to find in the dark.
- Constant memory returns lights to previous level after a power failure.
- Higher ratings
- Single pole and 3-way operation.
- Works with standard 3-way switches and wiring.
- Screw-pressure-plate backwire terminals save time, space and money.

RHDH163P

- No de-rating.
- No fins to break.

CATALOG NUMBER	DESCRIPTION	RATINGS	COLOR
FLUORESCENT PRESET, SINGLE POLE/3-WAY DIMMERS*			
RHFB83PTC	Preset, Single Pole/3-Way Three Interchangeable Face Colors	120V, 8A	Ivory/White/Light Almond
RHFB83PW	Preset, Single Pole/3-Way		White
FLUORESCENT PRESET, SINGLE POLE/3-WAY DIMMERS, 0-10V			
RH4FBL3PTC	Fluorescent Single Pole/3-Way Dimmer with Preset, 3 Interchangeable Face Colors	0-10V	Ivory/White/Light Almond
RH4FBL3PW	Fluorescent Single Pole/3-Way Dimmer with Preset	0-10V	White
FAN SPEED CONTROLS, DE-HUMMER, SINGLE POLE/3-WAY**			
RHDH163PTC†	Preset, Single Pole/3-Way Three Interchangeable Face Colors	120V, 1.6A	Ivory/White/Light Almond
RHDH163PW†	Preset, Single Pole/3-Way		White

*For use with Advance MK10 dimming ballasts. See instruction sheet for complete list of compatible ballasts.
**Feature specially designed capacitive circuitry to virtually eliminate fan motor "hum."
†Available in VisionPak™ packaging, add "CCV6" to Catalog Number. Example: RHDH163PTCCCV6.

DE-RATING CHART FOR RADIANT DIMMERS			
CATALOG NUMBER	MAXIMUM LOAD	MULTI-GANG DE-RATING	
		2 GANG	3 GANG
RH703P	700W	700W	700W
RH1103P	1100W	1100W	800W
RHLV703P	700VA	700VA	650VA
RHLV1103P	1100VA	950VA	700VA
RHFB83P	8A	8A	6.5A
RHDH163P	1.6A	1.6A	1.6A

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.