the **radiant**® *collection*
Wave® Switch

Wave Hello to Touchless Lighting Control

RSWV153, RSWV203

The radiant Wave Switch lets users turn lights on, or off, with just the wave of a hand, providing a germ-and-worry free, touchless solution that's perfect for homes, hotels, offices and more. From kitchens and bathrooms, to clinics or conference rooms, creating cleaner spaces starts with cleaner control. With a preset sensor distance of 4", this feature is easily adjustable to sense movement from 1" to 6" in front of the switch.

Features & Benefits



- **Part of the radiant® collection:** Pair with a radiant screwless wall plate for a sleek look.
- **Adjustable activation distance:** one (1) to six (6) inches.
- **Available in both 15A and 20A versions:** Allows for touchless control to fit any project or application.
- **Ground lead and wire nut provided for easy connection**
- **Neutral wire:** Accepts neutral wire when requied by NEC for new construction. Works in retrofit applications where a neutral wire may not be available.
- **Replaces any standard single pole or 3-way switch.**
- **Accepts #12 and #14 AWG.**

3rd Party Compliance

cULus Listed, UL508, Conforms to NEMA WD-1 and WD-6, File Number E350248.
Standard CSA C22.2 No. 14

Ordering Information

Catalog Number	Description	Color	Rating	COO	UPC
RSWV153	Single-Pole/3-Way Wave Switch	Black	15A, 120VAC, 1/2 HP	China	785007382525
RSWV203	Single-Pole/3-Way Wave Switch	Black	20A, 120VAC, 3/4 HP	China	785007382518

Technical Information

Performance		
Electrical		
Ratings	RSWV153	15A Resistive, 15A General Purpose, 15A Incandescent, 15A Standard Ballast, 15A Electronic Ballast, 1/2 HP
	RSWV203	20A Resistive, 20A General Purpose, 20A Incandescent, 20A Standard Ballast, 16A Electronic Ballast, 3/4 HP
Voltage		120VAC
Horse Power (HP)		15A: 1/2 HP 20A: 3/4 HP
Environment		Indoor Use Only
Mechanical		
Terminal Accommodation		#14-12 AWG solid and stranded copper wire
Environmental		
Flammability		UL94 V2
Operating Temperature		Maximum ambient temperature not to exceed 35°C (95°F).
Materials		
Enclosure Material		Impact-resistant thermoplastic
RoHS Compliant		Yes



RSWV203

Warranty
1 Year

Vertical Markets

- Residential
- Multiple Dwelling
- Hospitality/Lodging
- Healthcare
- Office
- Education

Also available in the radiant® collection...

- Lighting & Fan Controls
- Paddle Switches
- Tamper-Resistant & Standard Duplex Receptacles
- GFCI Receptacles
- Sensors
- USB Charging Devices
- Combination Devices
- Night Lights
- Home Automation Controls
- Screwless Wall Plates

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

905.738.9195
www.legrand.ca

FOLLOW US

CS3212 February 2022 © Legrand All Rights Reserved