



Pass and Seymour
20A, 125V Watertight Straight Blade Plug, Yellow
Part No. 14W33



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Color-coded sealing bushings provided for a large range of cord diameters.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | United States | Application Sector | Commercial |
| Standard | UL 498 | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.85 in | Product Depth US | 2.62 in |
|------------------|---------|------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|--------|
| CSA Listed | Yes | CSA File Number | 701645 |
|------------|-----|-----------------|--------|

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 20 A |
|-----------------|---|----------|------|

Number of Poles

Double Pole

Wire Size

14 - 12 AWG

Voltage

125.0 V
