



Tamper-Resistant Display Receptacle, 15A 125V With Brass Plate and plug.

Features & Benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly
- Easily accessed break-off line contact connecting tab for fast and easy split circuit wiring
- .032 inch thick brass triple-wipe power contacts for lasting retention
- Auto-ground clip assures positive ground

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
Finish	Metallic	Country Of Origin	United States
Receptacle Type	5-15R	Number of Receptacles	1
Features	Recessed	Outlet Type	Commercial
Package Quantity	1	Application Sector	Commercial
Standard	cULus	Type	Outlet

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

RoHS Conformant Yes

Technical Information

Is Tamper-Resistant Yes Amperage 15 A

Is Weather Resistant No Indoor/Outdoor Indoor

Voltage 125.0 V Connection Type Wired

Environmental Conditions 85% (relative humidity, non-condensing)
