



19.75"W x 38.25"H x 25.00"D

## Features & Benefits

Swing-EZ Wall Racks offer flexibility: The 25" deep unit gives the flexibility of mounting equipment where space is a premium and a full size rack cannot be used for small offices.

12-24 threaded EIA hole pattern: Standards compliant to mount numerous types of 19" panels and equipment.

Reinforcement pan attached to bottom of Swing-EZ: Sturdy and holds equipment up to 150lbs.

Self squaring assembly: No additional tools required

Front swing gate with latch pins and bolts on both: Allows you to open swing gate either left or right and easy access to rear of panels and equipment.

Side panels fold flat for shipping: Unfold for easy on site assembly.

Base includes 3" feed through holes: Allows cable delivery from bottom of rack.

- Includes 12-24 mounting screws: Do not have to purchase as separate item

## Specifications

### General Info

Product Line	Ortronics	Color	Black
UPC Number	662875580997	Country Of Origin	United States
Application Sector	Commercial	Type	Rack

### Dimensions

Product Width US	19.75 in	Product Depth US	25.0 in
Product Height US	35.0 in		

### Additional Information

---

RoHS Conformant

Yes

Product Environmental Profile

Yes

---